


TIPS

ET SERIES TIPS FOR PES51 SOLDERING PENCIL TINNED WITH LEAD FREE SOLDER


THE WELLER ADVANTAGE:

The sensor hole in the base of the tip is fitted with a stainless steel liner to prevent the tip from seizing to the sensor.




SCREWDRIVER

Cat No.	A		B		C	
	IN.	MM	IN.	MM	IN.	MM
ETA*	0.062	1.60	0.032	0.81	0.625	15.90
ETB*	0.093	2.40	0.020	0.51	0.625	15.90
ETC*	0.125	3.20	0.027	0.69	0.625	15.90
ETD	0.187	4.80	0.035	0.89	0.625	15.90
ETH	0.031	0.80	0.019	0.48	0.625	15.90




LONG SCREWDRIVER

Cat No.	A		B		C	
	IN.	MM	IN.	MM	IN.	MM
ETJ	0.031	0.80	0.012	0.30	1.000	25.40
ETK*	0.046	1.20	0.026	0.66	1.000	25.40
ETL	0.078	2.00	0.027	0.69	1.000	25.40
ETM	0.125	3.20	0.037	0.94	1.000	25.40



NARROW SCREWDRIVER

Cat No.	A		B		C	
	IN.	MM	IN.	MM	IN.	MM
ETR	0.062	1.60	0.044	1.12	0.625	15.90




CONICAL

Cat No.	A		B		C	
	IN.	MM	IN.	MM	IN.	MM
ETP*	0.031	0.80	0.012	0.30	0.625	15.90
ETT	0.024	0.60	0.036	0.91	0.625	15.90




LONG CONICAL

Cat No.	A		B		C	
	IN.	MM	IN.	MM	IN.	MM
ETO*	0.031	0.80	0.044	1.12	1.000	25.40
ETS*	0.015	0.40	--	--	1.000	25.40



SINGLE FLAT

Cat No.	A		B		C	
	IN.	MM	IN.	MM	IN.	MM
ETAA	0.062	1.60	0.040	1.02	0.625	15.90
ETBB	0.093	2.40	0.032	0.81	0.625	15.90
ETCC	0.125	3.20	0.032	0.81	0.625	15.90
ETDD	0.187	4.80	0.032	0.81	0.625	15.90
ETU	0.015	0.40	--	--	0.700	17.80
ETV	0.024	0.60	--	--	0.700	17.80



KNIFE

Cat No.	A		B		C	
	IN.	MM	IN.	MM	IN.	MM
ETKN	0.180	4.57	0.064	1.63	0.625	15.90

* Indicates available bulk (100 multiples only)