

Connectors for Use in Data, Signal, Control and Power Applications

MOLEX INC

E152602

MOLEX INDUSTRIAL DIV

4650 62ND AVE N

PINELLAS PARK, FL 33781 USA

Snap plugs, Avikrimp Series, Cat. No. A-5 followed by 59 or 69; Cat. No. B-5 followed by 79, 79B, 89 or 89B; Cat. No. A-8 followed by 59 or 69; Cat. No. B-8 followed by 79 or 89. Insulkrimp Series, Cat. No. A-2 followed by 59X or 69X; Cat. No. B-2 followed by 79X or 89X, and SPL-0515. Krimptite Series, Cat. No. A-1 followed by 59 or 69; Cat. No. B-1 followed by 79 or 89.

Snap plug receptacles, Insulkrimp Series, Cat. No. BRA-21 followed by 56 or 80, may be followed by NDK; Cat. No. BRB-21 followed by 56 or 80, may be followed by N; Avikrimp Series, Cat. No. BRA-81 followed by 56, may be followed by N or NDK, may be preceded by "S"; Cat. No. BRA-81 followed by 80, may be followed by N, may be preceded by "S"; Cat. No. BRB-81 followed by 56, may be followed by N or NDK, may be preceded by "S"; Cat. No. BRB-81 followed by 80, may be followed by N, may be preceded by "S". Cat. No. AA-11 followed by 20 or 21; Cat. No. BB-11 followed by 22 or 23.

All Cat. Nos. may be followed by C or T.

Connectors, Loose piece terminal Part Nos. 194031130 and 194031241, Strip carried terminal Part Nos. 194031131 and 194031240, and SC Header housing Part Nos. 194031120, 194031230 and 194160003.

Splitter box assembly Part No. 19424-0002, Housing Part No. 19424-0001, Header Part No. 19403-1120, Loose piece terminal Part No. 19403-1133 and Strip carried terminal Part No. 19403-1132.

Model No. 19418 followed by -0001, -0002, -0004, -0005, -0007, -0008, -0010, -0011, -0013 and -0014; Model No. 19419 followed by -0001, -0002, -0005, -0007, -0008, -0011, -0012, -0014 and -0015; Model No. 19429 followed by -0005, -0009, -0010, -0011, -0014, -0033, -0035, -0036, -0037, -0038, -0041, -0043, -0044, -0045, -0046.

Connectors, Part Nos. 192950002, 192950004, 192970001, 192970002.

Marking: Company name or trademark "MX-ETC" or "ETC" and catalog designation on device or carton.

Last Updated on 2005-02-11

Connectors for Use in Data, Signal, Control and Power Applications

The devices covered under this category are incomplete in certain constructional features or restricted in performance capabilities and are intended for use as components of complete equipment submitted for investigation rather than for direct separate installation in the field. THE FINAL ACCEPTANCE OF THE COMPONENT IS DEPENDENT UPON ITS INSTALLATION AND USE IN COMPLETE EQUIPMENT SUBMITTED TO UNDERWRITERS LABORATORIES INC.

GENERAL

This category covers single and multipole connectors for factory assembly to copper conductors or printed wiring boards for use in data, signal, control and power applications within and between electrical equipment. These connectors may employ crimp terminals, solder terminals, quick-connect terminals, insulation displacement or insulation piercing terminals, pressure terminal connectors, wire-binding screws, or other terminals that are intended for factory wiring.

Where only the catalog or series designation are indicated in the individual Recognitions, the ratings and Conditions of Acceptability are contained in the Recognition Report.

Ratings — Unless otherwise noted in the individual Recognitions, these devices have not been evaluated for current interruption (making or breaking a mated connection under load), nor for connection to branch circuit receptacle outlets. Devices without a specified electrical rating have not been tested for current carrying capability and should be evaluated in the end-use product. Devices covered under this category are eligible for assigned ratings up to 200 A and up to 600 V ac or dc. Devices with assigned electrical ratings have been investigated for their current-carrying capability under conditions representing the manufacturer's intended use with operating temperatures not exceeding the connector's insulating material or terminated conductors.

Unless otherwise noted in the individual Recognitions, conductor secureness testing has been performed on crimp contacts at 20 lbf for 18 AWG or larger conductors and 8 lbf for smaller conductors using stranded copper conductors.

Unless otherwise specified in the individual Recognitions, the connections between an insulation piercing or insulation displacement terminal and the conductors of a flexible cord, ribbon cable or wire have not been evaluated. The electrical and mechanical properties of the connection should be subjected to testing based upon the requirements for the end-use product.

The connections between a printed circuit board or solder terminal and the traces on a printed wiring board or the conductors of a flexible cord, ribbon cable or wire have not been evaluated. The electrical and mechanical properties of the connection should be subjected to testing based upon the requirements for the end-use product.

Clips, flanges, screws or other mounting hardware have not been evaluated for their ability to secure the connector in place and should be evaluated in the end-use product.

Unless otherwise noted in the individual Recognitions, these devices have not been evaluated for use in equipment grounding applications.

Spacings — Unless otherwise specified in the individual Recognitions, spacings through air or over surfaces are 1.2 mm minimum for a device rated 250 V or less, and 3.2 mm minimum for a device rated more than 250 V.

Hybrid Device — A device employing dedicated contacts of two or more rating designations.

Insulating Materials — The insulating materials used in devices rated less than 8.3 A and less than 30 rms (less than 42 peak) have been evaluated for their Relative Thermal Index (Electrical and Mechanical without impact). In addition to Relative Thermal Index, devices rated 8.3 A - 200 A, 30 - 600 V have been evaluated for Flame Rating. The maximum operating temperature for any connector shall not exceed the rated operating temperature that is based on the Relative Thermal Index of the material.

Devices marked with a flammability class have demonstrated compliance with the applicable flame class as describe in UL 94, "Tests for Flammability of Plastic Materials for Parts in Devices and Appliances."

CONDITIONS OF ACCEPTABILITY

Consideration is to be given to the Conditions of Acceptability specified in the individual Recognitions when the components are employed in the end-use equipment.

REQUIREMENTS

The basic standard used to investigate products in this category is UL 1977, "Component Connectors for Use in Data, Signal, Control and Power Applications."

Last Updated on 2002-02-08

This page and all contents are Copyright © 2005 by Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2005 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.



Online Certifications Directory - Notice of Disclaimer

By accessing these Listings, Designs, Constructions, Systems, and Assemblies, the user acknowledges and accepts the terms and conditions upon which this service is made available.

THIS INFORMATION AND ALL RELATED MATERIALS, SUPPORT, AND SERVICES ARE MADE AVAILABLE BY UL FOR USE ONLY BY USERS FOR THEIR INTERNAL PURPOSES AND IS "AS IS," WITHOUT ANY REPRESENTATION OR WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

UL cannot and does not warrant that this information is current, accurate, or complete. This database contains the names of companies who have qualified to use the UL Mark and those products for which samples have been evaluated by UL and judged to be eligible for Listing. The manufacturer is not obligated to label all of his production. Accordingly, the appearance of a company's name or product in this database does not in itself assure those products are covered under UL's Listing and Follow-Up Service. Only those products bearing the appropriate UL Mark should be considered covered under UL's Listing and Follow-Up Service. Any reproduction or re-transmission of this information is prohibited unless reproduced or re-transmitted in its entirety, including this Notice of Disclaimer.

UL does not permit hyperlinking to this website without its express prior written consent and the execution of a *hyperlinking agreement*.