

## Classic ECO Candle

CLECO CAN 240V 18W B22 SV1

0023850

### Range features



CE

### PRODUCT OVERVIEW

Light colour	828 Homelight
Technology	Halogen
Ordering number	0023850
Average life (Rated) (h)	2000
Energy class	D
Lamp shape	Candle
Lamp finish	Clear
Dimmable	Yes
Cap/Base	B22
Type	Candle ECO
EAN code	5410288238500
CRI (Ra)	100
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	205
Watt (Nominal) (W)	18
Equivalent watt (W)	24
Voltage (V)	240

# Classic ECO Candle

CLECO CAN 240V 18W B22 SV1

**0023850**

## DATA TABLE

### General data

Ordering number	0023850
Technology	Halogen
Average life (Nominal) (h)	2000
Average life (Rated) (h)	2000
Energy saving lamp	No
Energy class	D
Lamp shape	Candle
Lamp finish	Clear
Dimmable	Yes
Cap/Base	B22
Type	Candle ECO
EAN code	5410288238500
Product name	CLECO CAN 240V 18W B22 SV1
Lamp mercury content (mg)	0
Starting time (max) (s)	0.01
Warm-up time to 60% of full light (max) (s)	Instant full light
Control gear required	No
Fixture rating	Open
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-2
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	> 8000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

### Optical data

Light colour	828 Homelight
CRI (Ra)	100
Suitable for accent lighting	No
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	205
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	205

## Classic ECO Candle

CLECO CAN 240V 18W B22 SV1

0023850

### Electrical data

<b>kWh per 1000 hours burning time</b>	18
<b>Watt (Rated) (W)</b>	18
<b>Watt (Nominal) (W)</b>	18
<b>Equivalent watt (W)</b>	24
<b>Voltage (V)</b>	240
<b>Lamp power factor</b>	1

### Physical data


<b>Weight (kg)</b>	0.02
<b>Lamp Length (mm) - C/L</b>	93.5
<b>Max. Lamp Diameter (mm) - D</b>	36
<b>Single packaging type</b>	Box/Sleeve
<b>Single package dimensions (L x W x H) (cm)</b>	9.80 x 3.50 x 3.50
<b>Inner package dimensions (L x W x H) (cm)</b>	19.00 x 8.00 x 11.00
<b>Inner package net weight (kg)</b>	0.19
<b>Outer package dimensions (L x W x H) (cm)</b>	43.00 x 21.50 x 25.00

## Classic ECO Candle

CLECO CAN 240V 18W B22 SV1

0023850

### TECHNICAL DRAWINGS



### ENERGY LABEL

