




8	7	6	5	4	3	2	EN-02J09
---	---	---	---	---	---	---	----------



 THIRD ANGLE PROJECTION		DIMENSIONS: ☐ mm INCH ☐ INCH mm ☒ mm ONLY		SHT	REV
				REVISE ON CAD ONLY	

MOLEX INCORPORATED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.

	EC NO. DRWN: CH'K: APPR:	
	EC NO. DRWN: CH'K: APPR:	
	EC NO. DRWN: CH'K: APPR:	
	EC NO. DRWN: CH'K: APPR:	
0	RELEASED 10/4/03/122 EC NO. J2004-3249 DRWN: Y.SAKIYAMA CH'K: M.SASAO APPR: M.SASAO	

DESCRIPTION	MATERIAL 材料	SHEET 2 OF 2 参照 REFER TO SHEET 2 OF 2
	FINISH 仕上り	SHEET 2 OF 2 参照 REFER TO SHEET 2 OF 2
REV	WIRE RANGE 適用電線範囲	—//—
	INS. RANGE 被覆外径	—//—

GENERAL TOLERANCES: (UNLESS SPECIFIED)		
一般公差		
10 UNDER 未満		±0.2
10 OVER 以上	30 UNDER 未満	±0.25
30 OVER 以上		±0.3
ANGLE	角度	±3°

SCALE	DESIGN UNITS
--	☒ mm ☐ INCH
DRAWN BY & DATE	
Y.Sakiyama '04/03/22	
CHECKED BY & DATE	
M. Sasaki '04/03/22	
APPROVED BY & DATE	
M. Sasaki '04/03/22	
CAD FILENAME	
SD-55359-015.S01	
THIS DRAWING CONTAINS	
UNINCORPORATED AND SHOWN	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.

SD-55359-015.S01 Δ

△ ピン根元に適用する。
THIS DIMENSION TO BE MEASURED AT PIN BASE.

⑬ テールとネール、リヤネールを併せた平坦度は、0.1 MAX.とする。
TOTAL COPLANARITY OF SOLDER TAILS, NAILS
AND REAR-NAILS TO BE 0.1 MAX.

基板推奨寸法

RECOMMENDED P.C.B. LAYOUT

605 310-05253-0