



Datasheet

Stock No: 541-270

ENGLISH

# RS Pro 36.9 x 21.1mm Hand Rectangular Punch & Die Combinations



## Features:

### Square, Rectangular and Radius Hole Cutters

Square, rectangular and radius (rounded corner) hole cutters suitable for use on mild steel (28 tons/in<sup>2</sup> uts max) up to 1.6mm (16 swg) and aluminium up to 2mm (14 swg) except as marked \* (in which case capacity is 18 swg/1.22mm mild steel)

- Long life punches with minimum burr, distortion or surface damage
- Easy to dismantle - slugs drop freely out of die
- Most punches can be used with the hydraulic pump/cylinder Stock no 605-223 or hydraulic hand punch kit Stock no 388-3628 up to 35mm/1 1/4 in diameter (See comparison table for exceptions). Not suitable for lever presses
- Ball race included

## Specifications:

Hole Shape:	Rectangular
Operation:	Hand
Hole Size:	36.9 x 21.1mm
Cutting Capacity:	Mild Steel: 1.6 mm; Aluminium: 2 mm