

10

9

8

7

6

5

4





3

2

1

注記 NOTES

1. 嵌合相手: 51146 シリーズ
MATES WITH: 51146 SERIES
2. ロック窓は2、3極品は1箇所、4極品以上は2箇所とする。
LOCKING WINDOW: ONE PLACE FOR 2 AND 3 CIRCUIT PRODUCTS
AND TWO PLACES FOR MORE THAN 3 CIRCUIT PRODUCTS.
3. 基準面 [V] からのソルダーテールと金具の半田付け面のズレ量は、
上方向に 0.05MAX.、下方向 0.15MAX.、とし、20 極以下の相互の
バラツキ量は 0.1MAX. とする。
MISALIGNMENT OF SOLDER TAIL AND FITTING NAIL FROM [V]
: UPPER DIRECTION 0.05MAX.
: LOWER DIRECTION 0.15MAX.
: OFFSET BETWEEN UPPER AND LOWER 0.1MAX. (UNDER 20 CKTS.)
4. 偶数極の製品に適用。
APPLY EVEN CIRCUIT PRODUCTS.
5. 材質 MATERIAL
ウエハー: WAFER: PPS, UL94V-0
ピン: リン青銅 PIN: PHOSPHOR BRONZE
コンタクト部: 金メッキ 0.2 マイクロメートル以上
CONTACT AREA: GOLD 0.2 MICROMETER MINIMUM
テール部: 銅メッキ 3.0 マイクロメートル以上
TAIL AREA: TIN 3.0 MICROMETER MINIMUM
下地メッキ: ニッケルメッキ 1.0 マイクロメートル以上
UNDER PLATING: NICKEL 1.0 MICROMETER MINIMUM
金具: リン青銅 FITTING NAIL: PHOSPHOR BRONZE
銅メッキ 3.0 マイクロメートル以上
TIN 3.0 MICROMETER MINIMUM
下地メッキ: ニッケルメッキ 1.0 マイクロメートル以上
UNDER PLATING: NICKEL 1.0 MICROMETER MINIMUM
6. 本製品は 53780-**-**10/-**-**18 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 53780-**-**10/-**-**18.
7. ELV 及び RoHS 適合品
ELV & RoHS COMPLIANT.

参考基板レイアウト
RECOMMENDED P.C. BOARD PATTERN DIM. (REF.)ウエハー
WAFER
トレードマーク
TRADE MARK

16.25	22.5	38.77	36.25	42.65	53780-3070	30
8.75	22.5	26.27	23.75	30.15	-2070	20
7.5	20	23.77	21.25	27.65	-1870	18
6.25	16.25	20.02	17.5	23.9	-1570	15
5	15	18.77	16.25	22.65	-1470	14
3.75	12.5	16.27	13.75	20.15	-1270	12
2.5	10	13.77	11.25	17.65	-1070	10
2.5	8.75	12.52	10	16.4	-0970	9
1.25	7.5	11.27	8.75	15.15	-0870	8
1.25	6.25	10.02	7.5	13.9	-0770	7
—	5	8.77	6.25	12.65	-0670	6
—	3.75	7.52	5	11.4	-0570	5
—	2.5	6.27	3.75	10.15	-0470	4
—	—	5.02	2.5	8.9	-0370	3
—	—	3.77	1.25	7.65	53780-0270	2
E	D	C	B	A	EMBOSSD PACKAGE	CKT.
—					オーダー番号 ORDER No.	極数

CONNECTOR SERIES NO. 53780-**-19

REVISED EC NO: J2010-1927 DRWN: KUROSE CHKD: KASAKAWA APPR: NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	± 0.2	DRAWN BY T. UENO	DATE '04/04/15	TITLE 1.25 W/B CONN WAFER ASSY FOR SMT			
		10 OVER 30 UNDER	± 0.25	CHECKED BY M. SASAO	DATE '04/04/15				
		30 OVER	± 0.3	APPROVED BY M. SASAO	DATE '04/04/15				MOLEX INCORPORATED
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.			SHEET NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-53780-003			1 OF 2
REV		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

9

8

7


6

5


4

3


2





7~19極の奇数極に適用
APPLY FOR ODD CIRCUITS OF 7~19



8~30 極の偶数極に適用
APPLY FOR EVEN CIRCUITS OF 8~30




ロック形状図
LOCK CONFIGURATION




嵌合図 (SCALE 5:1)
MATED CONNECTORS (SCALE 5:1)

REVISED EC NO.: J2010-1927 DRWN:SKUR05E 2010/03/25 CHKD:KASAKAWA 2010/03/26 APPR:NUKITA 2010/03/29		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		CONNECTOR SERIES NO. 53780-**-19	
		10 UNDER ± 0.2		DRAWN BY DATE T. UENO '04/04/15		SCALE --- TITLE	
		10 OVER 30 UNDER ± 0.25		CHECKED BY DATE M. SASAO '04/04/15		DESIGN UNITS METRIC	
		30 OVER ± 0.3		APPROVED BY DATE M. SASAO '04/04/15		THIRD ANGLE PROJECTION	
DESCRIPTION		ANGULAR ± 3 °		MOLEX MOLEX INCORPORATED		1.25 W/B CONN WAFER ASSY FOR SMT	
REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE CHART		DOCUMENT NO. SD-53780-003	
				SIZE A3		SHEET NO. 2 OF 2	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							




DETAIL F



NOTES

1. 梱包数量: 1500個/リール
NUMBER OF CONNECTORS : 1500PCS/REEL



3. トップテープの剥離強度： 0.1N ～ 1.3N(10gf ～ 130gf)
(剥離方向は下図参照)
尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE : 0.1N ～ 1.3N(10gf ～ 130gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED .DURING TRANSPORTATION.



4. 材料(MATERIAL)
 キャリアテープ(CARRIER TAPE): ポリプロピレン(POLYPROPYLENE)
 トップテープ(TOPTAPE): PET, PE, PEF
 リール(REEL): ポリスチレン(PS) <リサイクル材を含む>
 POLYSTYRENE(PS) <RECYCLE MATERIAL CONTAINED>
5. 本製品は 53780- **90/- **80 の鉛フリー品である。
 THIS PRODUCT IS LEAD FREE OF 53780-**90/-**80.
6. ELV 及び RoHS 適合品
 ELV & RoHS COMPLIANT

REVISED	EC NO: J2010-0021	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	MODEL NO.	53780-***70
	DRWN:MTAKASAKI		2009/07/07	10 UNDER	± 0.2	DRAWN BY T. UENO	DATE '04/04/15	TITLE 1.25 W/B WAFER ASSY EMBOSSSED TAPE PACKAGE	 THIRD ANGLE PROJECTION	
	CHKD:MHAYASHI		2009/07/08	10 OVER 30 UNDER	± 0.25	CHECKED BY M. SASAO	DATE '04/04/15			
	APPR:NUKI TA		2009/07/08	30 OVER	± 0.3	APPROVED BY M. SASAO	DATE '04/04/15			
				ANGULAR ±3 °	MATERIAL NO.	DOCUMENT NO.	SHEET NO.			
	B		REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE A3	SEE CHART	SD-53780-004	1 OF 3		
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										

10

9

8

7

6



5

4


3

2

1



引き出し方向
PULL OUT DIRECTION



11.5	24	29.4	25.4	11.75	16.7	53780-0970	9
				10.5	15.45	53780-0870	8
				9.25	14.2	53780-0770	7
				8	12.95	53780-0670	6
				6.75	11.7	53780-0570	5
7.5	16	21.4	17.4	5.5	10.45	53780-0470	4
				4.25	9.2	53780-0370	3
(F)	E	D	C	3	7.95	53780-0270	2
キャリアテープ幅 CARRIER TAPE WIDTH				(B)	(A)	MATERIAL NO.	種数 CKT.
				MODEL NO.		53780-***70	

REVISED EC NO.: J2010-0021 DRWN:MTAKASAKI CHKD:MHAYASHI APPR:NUKITA REV B	DESCRIPTION 2009/07/07 2009/07/08 2009/07/08	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		10 UNDER	± 0.2	DRAWN BY T. UENO	DATE '04/04/15	TITLE 1.25 W/B WAFER ASSY EMBOSSD TAPE PACKAGE			
		10 OVER 30 UNDER	± 0.25	CHECKED BY M. SASAO	DATE '04/04/15				
		30 OVER	± 0.3	APPROVED BY M. SASAO	DATE '04/04/15	MOLEX INCORPORATED			
		ANGULAR ±3 °		MATERIAL NO.					
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-53780-004		2 OF 3		
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

9

8

7



6

5

4

3

2



26.2	52.4	56	61.4	57.4	38	42.95	53780-3070	30
20.2	40.4	44	49.4	45.4	25.5	30.45	53780-2070	20
					25.5	27.95	53780-1870	18
					19.25	24.2	53780-1570	15
					18	22.95	53780-1470	14
					15.5	20.45	53780-1270	12
14.2	28.4	32	37.4	33.4	13	17.95	53780-1070	10
(G)	F	E キャリアテープ幅 CARRIER TAPE WIDTH	D	C	(B)	(A)	MATERIAL NO.	極数 CKT.

REVISED	EC NO: J2010-0021 DRWN:MTAKASAKI CHKD:MAYASHI APPR:NUKITA	2009/07/07 2009/07/08 2009/07/08	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	MODEL NO. SD-53780-004		THIRD ANGLE PROJECTION	
				10 UNDER	±0.2	DRAWN BY T. UENO	DATE '04/04/15	TITLE 1.25 W/B WAFER ASSY EMBOSSD TAPE PACKAGE					
				10 OVER 30 UNDER	±0.25	CHECKED BY M. SASAO	DATE '04/04/15						
				30 OVER	±0.3	APPROVED BY M. SASAO	DATE '04/04/15	molex MOLEX INCORPORATED					
				ANGULAR ±3 °	MATERIAL NO.		DOCUMENT NO.						
B	REV			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-53780-004		3 OF 3			
				SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									