

Surge protection device - TT-ST-2-PE/S2-24DC - 2801458


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Double-level modular terminal block with two-stage surge protection for one two-wire impedance-sensitive signal circuit, separate ground connection, nominal voltage: 24 V DC.



Key commercial data

Packing unit	10 pc
GTIN	 4 046356 769204
Weight per Piece (excluding packing)	26.69 g
Custom tariff number	85365019
Country of origin	Germany

Technical data

Dimensions

Height	100 mm
Width	6.2 mm
Depth	63.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Degree of protection	IP20

General

Housing material	PA 6.6
Inflammability class according to UL 94	V0
Color	black
Standards for air and creepage distances	IEC 60664-1
Mounting type	DIN rail: 35 mm

Surge protection device - TT-ST-2-PE/S2-24DC - 2801458

Technical data

General

Type	Double-level terminal block
Number of positions	2
Direction of action	Line-Line & Line-Earth Ground

Protective circuit

IEC test classification	C1
	C2
	C3
	D1
VDE requirement class	C1
	C2
	C3
	D1
Nominal voltage U_N	24 V DC
Maximum continuous operating voltage U_C	30 V DC
	21 V AC
Nominal current I_N	6 A (40°C)
Operating effective current I_C at U_C	$\leq 1 \mu\text{A}$
Residual current I_{PE}	$\leq 1 \mu\text{A}$
Nominal discharge current I_n (8/20) μs (Core-Core)	300 A
Nominal discharge current I_n (8/20) μs (Core-Earth)	5 kA
Total surge current (8/20) μs	5 kA
Nominal pulse current I_{an} (10/1000) μs (Core-Core)	25 A
Nominal pulse current I_{an} (10/1000) μs (Core-Earth)	50 A
Impulse discharge current (10/350) μs , peak value I_{imp}	500 A (per path)
Output voltage limitation at 1 kV/ μs (Core-Core) spike	$\leq 45 \text{ V}$
Output voltage limitation at 1 kV/ μs (Core-Earth) spike	$\leq 800 \text{ V}$
Output voltage limitation at (8/20) μs (core-core)	$\leq 50 \text{ V}$ (at 300 A)
Output voltage limitation at (8/20) μs (core-earth)	$\leq 750 \text{ V}$ (at 500 A)
	$\leq 1.25 \text{ kV}$ (at 5 kA)
Residual voltage at I_n , (conductor-conductor)	$\leq 50 \text{ V}$ (at 300 A)
Residual voltage at I_n , (conductor-ground)	$\leq 750 \text{ V}$ (at 500 A)
	$\leq 1.25 \text{ kV}$ (at 5 kA)
Residual voltage with I_{an} (10/1000) μs (conductor-conductor)	$\leq 45 \text{ V}$ (at 25 A)
Residual voltage with I_{an} (10/1000) μs (conductor-ground)	$\leq 1.1 \text{ kV}$ (at 50 A)
Voltage protection level U_p (core-core)	$\leq 50 \text{ V}$ (C1 - 0,6 kV / 300 A)
	$\leq 45 \text{ V}$ (C3 - 25 A)
	$\leq 45 \text{ V}$ (1 kV/ μs)
Voltage protection level U_p (core-ground)	$\leq 1.25 \text{ kV}$ (C2 - 10 kV / 5 kA)
	$\leq 1.1 \text{ kV}$ (C3 - 50 A)
	$\leq 750 \text{ V}$ (C1 - 1 kV/500 A)

Surge protection device - TT-ST-2-PE/S2-24DC - 2801458

Technical data

Protective circuit

	≤ 800 V (1 kV/μs)
Response time tA (Core-Core)	≤ 1 ns
Response time tA (Core-Earth)	≤ 100 ns
Input attenuation aE, sym.	typ. 0.3 dB (330 kHz/150 Ω)
	typ. 0.3 dB (1.1 kHz/50 Ω)
Cut-off frequency fg (3 dB), sym. in 50 Ohm system	typ. 3.3 MHz
Cut-off frequency fg (3 dB), sym. in 150 Ohm system	typ. 1 MHz
Capacity (Core-Core)	≤ 2 nF
Surge protection fault message	None
Max. required back-up fuse	6.3 A (T/IEC 60127-2/3)
Impulse durability (conductor-conductor)	C1 - 0,6 kV / 300 A C3 - 25 A
Impulse durability (conductor-ground)	C2 - 10 kV/5 kA D1 - 500 A C1 - 1 kV/500 A C3 (50 A)
Pulse reset time (conductor-ground)	≤ 700 ms, at U _c and 10 A
Overload failure mode (conductor-conductor)	Mode 2

Connection data

Connection method	Spring-cage connection
Connection type IN	Spring-cage
Connection type OUT	Spring-cage
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Connection, equipotential bonding

Connection method	Spring-cage connection
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Surge protection device - TT-ST-2-PE/S2-24DC - 2801458

Classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130807
eCl@ss 7.0	27130807
eCl@ss 8.0	27130807

ETIM

ETIM 3.0	EC000943
ETIM 4.0	EC000943
ETIM 5.0	EC000943

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

Approvals

Approvals

Approvals

UL Listed / GL

Ex Approvals

Approvals submitted

Approval details

UL Listed

GL

Surge protection device - TT-ST-2-PE/S2-24DC - 2801458

Accessories

Accessories

End cover


End cover - TT-D-STTCO-BK - 2858894



End cover for TERMITRAB TT-ST-..., width: 2.2 mm, color: Black

Drawings

Dimensioned drawing



Circuit diagram

