






LOC	DIST	REVISIONS					
		REV	DATE	BY	CHKD	APPD	
AJ	16	A1	11MAR11	RK	HMR		



- 1 ZINC PER QQ-Z-363.
- 2 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 3 BERYLLIUM COPPER PER QQ-C-530.
- 4 BRASS PER ASTM-B-453.
- 5 BRASS PER ASTM-B-16.
- 6 NICKEL PLATE PER QQ-N-290, 3.81 μ m [.000150] MINIMUM THICK.
- 7 TIN PLATE PER ASTM-B-545, 3.81 μ m [.000150] MINIMUM THICK.
- 8 GOLD PLATE PER MIL-G-45204, 0.76 μ m [.000030] MINIMUM THICK.
- 9. SEE INSTRUCTION SHEET 408-2769.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA - 21APR2005	5222132-1	
		CHK J. HAVENER - 21APR2005	PART NUMBER	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. LIPPERT - 21APR2005	TE Connectivity	
		NAME	JACK, VERTICAL, PCB 75 OHM, SERIES BNC	
	0 PLC $\pm$ - 1 PLC $\pm$ - 2 PLC $\pm$ 0.20 [.008] 3 PLC $\pm$ - 4 PLC $\pm$ - ANGLES $\pm$ -	PRODUCT SPEC	-	
		APPLICATION SPEC	-	
MATERIAL SEE NOTES 1-5	FINISH SEE NOTES 6-8	WEIGHT -	SIZE A1	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV A1