

# Titanlite 397

## DESCRIPTION AND GENERAL PROPERTIES

- **Material** Nitrile
  - **Length (cm)** 27-31
  - **Thickness (mm)** 1.00
  - **Wrist** Knitted wrist
  - **Colour/Color** Yellow
  - **Interior finish** Textile support
  - **Exterior finish** Smooth
  - **Size / EAN** 6 7 8 9 10
  - **Packaging** 1 pairs/bag - 10 pairs/bag - 100 pairs/carton
  - **Complementary information** Guaranteed without silicone
- Available in single pack and in polybag of 10 pairs  
Guaranteed without DMF



## PERFORMANCE RESULTS


### Certification category 2




4111X

### Legends

#### EN 388 MECHANICAL HAZARDS



#### EN 407 THERMAL RISKS heat and fire



#### CHEMICAL RISKS

##### EN ISO 374-1 Type A



U V W X Y Z

- A Methanol
- B Acetone
- C Acetonitrile
- D Dichloromethane
- E Carbon Disulfide
- F Toluene
- G Diethylamine
- H Tetrahydrofurane
- I Ethyl acetate

##### EN ISO 374-1 Type B



X Y Z

- J n-Heptane
- K Sodium hydroxide 40%
- L Sulphuric acid 96%
- M Nitric acid 65%
- N Acetic acid 99%
- O Ammonia 25%
- P Hydrogen peroxide 30%
- S Hydrofluoric acid 40%
- T Formaldehyde 37%

##### EN ISO 374-1 Type C



CUT

#### CUT RESISTANCE

- |             |             |             |
|-------------|-------------|-------------|
| A1 ≥ 200 G  | A4 ≥ 1500 G | A7 ≥ 4000 G |
| A2 ≥ 500 G  | A5 ≥ 2200 G | A8 ≥ 5000 G |
| A3 ≥ 1000 G | A6 ≥ 3000 G | A9 ≥ 6000 G |

#### MICRO-ORGANISMS

##### EN ISO 374-5



Protection against bacteria,  
fungi

##### EN ISO 374-5



Protection against bacteria,  
fungi, virus

VIRUS

##### EN 511



#### COLD HAZARDS

PERFORMANCE LEVELS

- 0-4 0-4 0 or 1
- Water permeability  
Contact cold resistance  
Convective cold resistance

##### EN 421



RADIOACTIVE  
CONTAMINATION

For more details: [www.mapa-pro.com](http://www.mapa-pro.com)

**MAPA**<sup>®</sup>  
PROFESSIONNEL

## SPECIFIC ADVANTAGES

- Excellent comfort, due to the thickness of the cotton lining and the ventilated back
- Freedom of movement: dexterity and flexibility, due to the close fit to the hand
- Excellent service life: good abrasion resistance

## MAIN FIELDS OF USE

### Automotive/mechanical industry

- Sanding
- Precision mechanical work
- Part assembly
- Handling oily mechanical parts

### Other industries

- Manufacturing small electrical components
- Construction materials handling

## INSTRUCTIONS FOR USE

### Instructions for use

- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use at workplace may differ from the « CE »-type-tests.
- It is not recommended for persons sensitized to dithiocarbamates and thiazoles to use these gloves.
- Put the gloves on dry, clean hands.
- Rub over the gloves stained with oil or grease before taking them off.
- Inspect the gloves for snags or tears before reusing them.

### Storage conditions

Store the gloves in their original packaging protected from light and humidity.

### Laundering conditions

Caution : using the gloves or submitting them to cleaning or laundering process which is not specifically recommended can alter their performance levels.

### Drying conditions

Ensure the inside of the gloves is dry before putting them on again.

## LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).

- CE-Type Examination Certificate

0075/014/162/10/17/1605

- Issued by the notified body nr

0075

C.T.C

4 rue Herman FRENKEL

F - 69367 LYON CEDEX 07