








LOC		DIST			REVISIONS					
CM		53	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD	
					AB		085-19 PER EC 0730-0137-96	7-1-97	JH	R5



1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
 2. RECOMMENDED PANEL THICKNESS 0.76 - 2.29.
 3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
- 4 OPTIONAL FOR KEYING HOUSING IN PANEL.
- 5 CIRCUIT NUMBER 1 LOCATION.
- 6 DIMENSION INDICATED IS AS MOLDED. ADDITIONAL GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR.
- 7 SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION.



3-DIMENSIONAL MODEL
NTS

4.45	.175	27.43	1.080
2.79	.110	14.35	.565
2.54	.100	13.97	.550
2.41	.095	13.46	.530
2.29	.090	13.21	.520
0.76	.030	8.64	.340
0.38	.015	8.13	.320
0.25	.010	7.62	.300
0.13	.005	6.35	.250
MM	IN	MM	IN

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

		COLOR		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13 3 PLC DEC ± - ANGLES ± 1°0'		DR 7-24-92 K. WHITAKER		AMP AMP Incorporated Harrisburg, PA 17105-3608	
		CHK 7-24-92 R. SWING			
		APPD 7-27-92 D. SELF			
		APPD 7-27-92 D. SELF			
MATERIAL NYLON,UL 94V-2		PRODUCT SPEC -		CAP,2 CIRCUIT, UNIVERSAL MATE-N-LOK™	
FINISH -		APPLICATION SPEC -			
		WEIGHT -			
		SIZE D	CAGE CODE 00779	DRAWING NO C-480699	
		SCALE 4:1		SHEET	1 OF 1

CUSTOMER DRAWING