




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	01						
			P4	REVISED PER ECO-11-004917	11MAR11	RK	HMR



- 1 - MATL: 1/2H BRASS OR NICKEL PL STEEL.
- 2 - NO BURRS PERMISSIBLE AT HOLE.
- 3 - MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
- 4 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225° F.
- 5 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.

- 1 FOR USE WITH MKII POSITIVE LOCK, LOW INSERTION FORCE FASTON RECEPTACLES AND MOST BUDGET FASTON RECEPTACLES.
- 2 PRELIMINARY - NOT FOR PRODUCTION
- 3 PREPRODUCTION - FASR REQUIRED
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



4 OBSOLETE	VO GREEN	2 1-520935-9
	VO BLACK	3 1-520935-8
4 OBSOLETE	VO BROWN	2 1-520935-7
	VO YELLOW	3 1-520935-6
	VO BLUE	1-520935-5
	VO RED	1-520935-2
	VO NATURAL	1-520935-1
	BLACK	2 520935-8
	BROWN	520935-7
	YELLOW	520935-6
	BLUE	520935-5
	GREEN	520935-4
	WEATHER RESIST BLACK	520935-3
	RED	520935-2
	NATURAL	520935-1
	COLOR	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	4/14/88	 TE Connectivity					
DIMENSIONS: INCHES		CHK	M FEHER	4/14/88						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	R KUZO	4/14/88	NAME HOUSING, RECPT, POSITIVE- LOCK & STANDARD FASTON, .250 SERIES, MKII					
		PRODUCT SPEC								
		APPLICATION SPEC								
		—								
MATERIAL	FINISH	WEIGHT			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		—			A2	00779	C=520935	—		
6/6 NYLON		SEE TABLE			CUSTOMER DRAWING					
					SCALE	4:1	SHEET	1 of 1	REV	P4