


Tapered roller bearings, single row, metric bearings



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass kg	Designation
d	D	T	dynamic C	static C_0		Reference speed r/min	Limiting speed		
mm			kN		kN	r/min			-
30	55	17	35,8	44	4,55	9000	12000	0,17	32006 X/Q



Calculation factors

e 0,43
 Y 1,4
 Y_0 0,8