



Digital extension XR06 Part number 88970215



- Power supply via the controller at the same voltage as the inputs
- Number of inputs/outputs can be configured in accordance with your requirements

	Type	Input	Output	Supply
88970211	XR06	4 digital	2 relays 8 A	Via the 24 V? controller
88970213	XR06	4 digital	2 relays 8 A	Via the 100? 240 V AC controller
88970214	XR06	4 digital	2 relays 8 A	Via the 24 V AC controller
88970215	XR06	4 digital	2 relays 8 A	Via the 12 V? controller
88970221	XR10	6 digital	4 relays 8 A	Via the 24 V? controller
88970223	XR10	6 digital	4 relays 8 A	Via the 100? 240 V AC controller
88970224	XR10	6 digital	4 relays 8 A	Via the 24 V AC controller
88970225	XR10	6 digital	4 relays 8 A	Via the 12 V? controller
88970231	XR14	8 digital	6 relays (4 x 8 A relay and 2 x 5 A relay)	Via the 24 V? controller
88970233	XR14	8 digital	6 relays (4 x 8 A relay and 2 x 5 A relay)	Via the 100? 240 V AC controller
88970234	XR14	8 digital	6 relays (4 x 8 A relay and 2 x 5 A relay)	Via the 24 V AC controller
88970235	XR14	8 digital	6 relays (4 x 8 A relay and 2 x 5 A relay)	Via the 12 V? controller

General environment characteristics for CB, CD, XD, XB, XR and XE product types

Certifications	UL, CSA? GL: except for 88 970 32x (pending)
Conformity with the low voltage directive	In accordance with 73/23/EEC: ? EN (IEC) 61131-2 (Open equipment)
Conformity with the EMC directive	In accordance with 89/336/EEC: ? EN (IEC) 61131-2 (Zone B) ? EN (IEC) 61000-6-2, ? EN (IEC) 61000-6-3 (*) ? EN (IEC) 61000-6-4? (*) Except configuration (88 970 1.1 or 88 970 1.2) + (88 970 250 or 88 970 270) + 88 970 241 class A (class B in a metal enclosure)
Earthing	Not included
Protection rating	In accordance with IEC/EN 60529: ? IP40 on front panel? IP20 on terminal block
Overvoltage category	3 in accordance with IEC/EN 60664-1
Pollution	Degree: 2 in accordance with IEC/EN 61131-2
Max operating Altitude	Operation: 2000 m? Transport: 3048 m
Mechanical resistance	Immunity to vibrations IEC/EN 60068-2-6, test Fc? Immunity to shock IEC/EN 60068-2-27, test Ea
Resistance to electrostatic discharge	Immunity to ESD? IEC/EN 61000-4-2, level 3
Resistance to HF interference	Immunity to radiated electrostatic fields? IEC/EN 61000-4-3? Immunity to fast transients (burst immunity) ? IEC/EN 61000-4-4, level 3? Immunity to shock waves? IEC/EN 61000-4-5? Radio frequency in common mode? IEC/EN 61000-4-6, level 3? Voltage dips and breaks (AC) ? IEC/EN 61000-4-11? Immunity to damped oscillatory waves? IEC/EN 61000-4-12
Conducted and radiated emissions	Class B (*) in accordance with EN 55022/11 group 1? (*) Except configuration (88 970 1.1 or 88 970 1.2) +? (88 970 250 or 88 970 270) + 88 970 241 class A (class B in a metal enclosure)
Operating temperature	-20? +55? C (+40? C in a non-ventilated enclosure) in accordance with? IEC/EN 60068-2-1 and IEC/EN 60068-2-2
Storage temperature	-40? +70? C in accordance with IEC/EN 60068-2-1 and? IEC/EN 60068-2-2
Relative humidity	95% max. (no condensation or dripping water) in accordance with? IEC/EN 60068-2-30
Mounting	On symmetrical DIN rail, 35 x 7.5 mm and 35 x 15 mm, or on panel (2 x? 4 mm)
Screw terminals connection capacity	Flexible wire with ferrule =? 1 conductor: 0.25 to 2.5 mm ² (AWG 24...AWG 14) ? 2 conductors 0.25 to 0.75 mm ² (AWG 24...AWG 18) ? Semi-rigid wire =? 1 conductor: 0.2 to 2.5 mm ² (AWG 25...AWG 14) ? Rigid wire =? 1 conductor: 0.2 to 2.5 mm ² (AWG 25...AWG 14) ? 2 conductors 0.2 to 1.5 mm ² (AWG 25...AWG 16) ? Tightening torque =? 0.5 N.m (4.5 lb-in) (tighten using screwdriver diam. 3.5 mm)

Processing characteristics of CB, CD, XD & XB product types

LCD display	CD, XD: Display with 4 lines of 18 characters
Programming method	Ladder or FBD/SFC (Grafcet)
Program size	Ladder: 120 lines? FBD: ? CB, CD: 350 typical blocks? XB, XD: 700 typical blocks
Program memory	Flash EEPROM
Removable memory	EEPROM
Data memory	368 bits/200 words
Back-up time in the event of power failure	Program and settings in the controller: 10 years? Program and settings in the plug-in memory: 10 years? Data memory: 10 years
Cycle time	Ladder: typically 20 ms? FBD: 6? 90 ms
Response time	Input acquisition time + 1 to 2 cycle times
Clock data retention	10 years (lithium battery) at 25? C
Clock drift	Drift < 12 min/year (at 25? C) ? 6 s/month (at 25? C with user-definable correction of drift)
Timer block accuracy	1%? 2 cycle times
Start up time on power up	< 1,2 s

Characteristics of products with AC power supplied

Supply	
Nominal voltage	24 V AC 100? 240 V AC

Operating limits	-15% / +20%? or 20.4 V AC? 28.8 V AC	-15% / +10%? or 85 V AC? 264 V AC
Supply frequency range	50/60 Hz (+4% / -6%) ? or 47? 53 Hz/57? 63 Hz	50/60 Hz (+4% / -6%) or 47? 53 Hz/57? 63 Hz
Immunity from micro power cuts	10 ms (repetition 20 times)	10 ms (repetition 20 times)
Max. absorbed power	CB12-CD12-XD10-XB10: 4 VA? CB20-CD20: 6 VA? XD10-XB10 with extension - XD26-XB26: 7.5 VA? XD26-XB26 with extension: 10 VA	CB12-CD12-XD10-XB10: 7 VA? CB20-CD20: 11 VA? XD10-XB10 with extension - XD26-XB26: 12 VA? XD26-XB26 with extension: 17 VA
Isolation voltage	1780 V AC	1780 V AC

Inputs

Input voltage	24 V AC (-15% / +20%)	100? 240 V AC (-15% / +10%)
Input current	4.4 mA @ 20.4 V AC? 5.2 mA @ 24.0 V AC? 6.3 mA @ 28.8 V AC	0.24 mA @ 85 V AC? 0.75 mA @ 264 V AC
Input impedance	4.6 k?	350 k?
Logic 1 voltage threshold	≥ 14 V AC	≥ 79 V AC
Making current at logic state 1	> 2 mA	> 0.17 mA
Logic 0 voltage threshold	≤ 5 V AC	≤ 20 V AC (≤ 28 V AC: XE10, XR06, XR10, XR14)
Release current at logic state 0	< 0.5 mA	< 0.5 mA
Response time with LADDER programming	50 ms? State 0? 1 (50/60 Hz)	50 ms? State 0? 1 (50/60 Hz)
Response time with function blocks programming	Configurable in increments of 10 ms? 50 ms min. up to 255 ms? State 0? 1 (50/60 Hz)	Configurable in increments of 10 ms? 50 ms min. up to 255 ms? State 0? 1 (50/60 Hz)
Maximum counting frequency	In accordance with cycle time (Tc) and input response time (Tr) : ? 1/ ((2 x Tc) + Tr)	In accordance with cycle time (Tc) and input response time (Tr) : ? 1/ ((2 x Tc) + Tr)
Sensor type	Contact or 3-wire PNP	Contact or 3-wire PNP
Input type	Resistive	Resistive
Isolation between power supply and inputs	None	None
Isolation between inputs	None	None
Protection against polarity inversions	Yes	Yes
Status indicator	On LCD screen for CD and XD	On LCD screen for CD and XD

Characteristics of relay outputs common to the entire range

Max. breaking voltage	5? 30 V? ? 24? 250 V AC
Breaking current	CB-CD-XD10-XB10-XR06-XR10: 8 A? XD26-XB26: 8 x 8 A relays, 2 x 5 A relays? XE10: 4 x 5 A relays? XR14: 4 x 8 A relays, 2 x 5 A relays
Electrical durability for 500 000 operating cycles	Utilization category DC-12: 24 V, 1.5 A? Utilization category DC-13: 24 V (L/R = 10 ms), 0.6 A? Utilization category AC-12: 230 V, 1.5 A? Utilization category AC-15: 230 V, 0.9 A
Max. Output Common Current	12 A for O8, O9, OA
Minimum switching capacity	10 mA (at minimum voltage of 12 V)
Minimum load	12 V, 10 mA
Maximum rate	Off load: 10 Hz? At operating current: 0.1 Hz
Mechanical life	10,000,000 (operations)
Voltage for withstanding shocks	In accordance with IEC/EN 60947-1 and IEC/EN 60664-1: 4 kV
Response time	Make 10 ms? Release 5 ms
Built-in protections	Against short-circuits: None? Against overvoltages and overloads: None
Status indicator	On LCD screen for CD and XD

Characteristics of product with DC power supplied**Supply**

Nominal voltage	12 V?	24 V?
Operating limits	-13% / +20%? or 10.4 V? ? 14.4 V? (including ripple)	-20% / +25%? or 19.2 V? ? 30 V? (including ripple)
Immunity from micro power cuts	≤ 1 ms (repetition 20 times)	≤ 1 ms (repetition 20 times)
Max. absorbed power	CB12 with solid state outputs: 1.5 W? CD12: 1.5 W? CD20: 2.5 W? XD26-XB26: 3 W? XD26-XB26 with extension: 5 W? XD26 with solid state outputs: 2.5 W	CB12-CD12-CD20 with solid state outputs - XD10-XB10 with solid state outputs: 3 W? XD10-XB10 with relay outputs: 4 W? XD26-XB26 with solid state outputs: 5 W? CB20-CD20 with relay outputs - XD26 with relay outputs: 6 W? XD10-XB10 with extension: 8 W? XD26-XB26 with extension: 10 W
Protection against polarity inversions	Yes	Yes

Digital inputs (I1 to IA and IH to IY)

Input voltage	12 V? (-13% / +20%)	24 V? (-20% / +25%)
Input current	3.9 mA @ 10.44 V? ? 4.4 mA @ 12.0 V? ? 5.3 mA @ 14.4 V?	2.6 mA @ 19.2 V? ? 3.2 mA @ 24 V? ? 4.0 mA @ 30.0 V?
Input impedance	2.7 k?	7.4 k?
Logic 1 voltage threshold	≥ 7 V?	≥ 15 V?
Making current at logic state 1	≥ 2 mA	≥ 2.2 mA
Logic 0 voltage threshold	≤ 3 V?	≤ 5 V?
Release current at logic state 0	< 0.9 mA	< 0.75 mA
Response time	1? 2 cycle times	1? 2 cycle times
Maximum counting frequency	Inputs I1 & I2: Ladder (1 kHz) & FBD (up to 6 kHz) ? Inputs I3 to IA & IH to IY: In accordance with cycle time (Tc) and input response time (Tr) : 1/ ((2 x Tc) + Tr)	Inputs I1 & I2: Ladder (1 kHz) & FBD (up to 6 kHz) ? Inputs I3 to IA & IH to IY: In accordance with cycle time (Tc) and input response time (Tr) : 1/ ((2 x Tc) + Tr)
Sensor type	Contact or 3-wire PNP	Contact or 3-wire PNP
Conforming to IEC/EN 61131-2	Type 1	Type 1
Input type	Resistive	Resistive
Isolation between power supply and inputs	None	None
Isolation between inputs	None	None
Protection against polarity inversions	Yes	Yes
Status indicator	On LCD screen for CD and XD	On LCD screen for CD and XD

Analogue or digital inputs (IB to IG)

CB12-CD12-XD10-XB10	4 inputs IB? IE	4 inputs IB? IE
CB20-CD20-XB26-XD26	6 inputs IB? IG	6 inputs IB? IG

Inputs used as analogue inputs

Measurement range	(0? 10 V) or (0? V power supply)	(0? 10 V) or (0? V power supply)
Input impedance	14 k?	12 k?
Input voltage	14.4 V? max.	30 V? max.

Value of LSB	14 mV, 4 mA	29 mV, 4 mA
Input type	Common mode	Common mode
Resolution	10 bits at max. input voltage	10 bits at max. input voltage
Conversion time	Controller cycle time	Controller cycle time
Accuracy at 25 °C	? 5%	? 5%
Accuracy at 55 °C	? 6.2%	? 6.2%
Repeat accuracy at 55 °C	? 2%	? 2%
Isolation between analogue channel and power supply	None	None
Cable length	10 m maximum, with shielded cable (sensor not isolated)	10 m maximum, with shielded cable (sensor not isolated)
Protection against polarity inversions	Yes	Yes
Potentiometer control	2.2 k? /0.5 W (recommended) ? 10 k? max.	2.2 k? /0.5 W (recommended) ? 10 k? max.

Inputs used as digital inputs

Input voltage	12 V? (-13% / +20%)	24 V? (-20% / +25%)
Input current	0.7 mA @ 10.44 V? ? 0.9 mA @ 12.0 V? ? 1.0 mA @ 14.4V?	1.6 mA @ 19.2 V? ? 2.0 mA @ 24.0 V? ? 2.5 mA @ 30.0 V?
Input impedance	14 k?	12 k?
Logic 1 voltage threshold	≥ 7 V?	≥ 15 V?
Making current at logic state 1	≥ 0.5 mA	≥ 1.2 mA
Logic 0 voltage threshold	≤ 3 V?	≤ 5 V?
Release current at logic state 0	≤ 0.2 mA	≤ 0.5 mA
Response time	1? 2 cycle times	1? 2 cycle times
Maximum counting frequency	In accordance with cycle time (Tc) and input response time (Tr) : ? 1/ (2 x Tc) + Tr)	In accordance with cycle time (Tc) and input response time (Tr) : ? 1/ (2 x Tc) + Tr)
Sensor type	Contact or 3-wire PNP	Contact or 3-wire PNP
Conforming to IEC/EN 61131-2	Type 1	Type 1
Input type	Resistive	Resistive
Isolation between power supply and inputs	None	None
Isolation between inputs	None	None
Protection against polarity inversions	Yes	Yes
Status indicator	On LCD screen for CD and XD	On LCD screen for CD and XD

Characteristics of relay outputs common to the entire range

Max. breaking voltage	5? 30 V? ? 24? 250 V AC
Max. Output Common Current	12A (10A UL) for O8, O9, OA
Breaking current	CB-CD-XD10-XB10-XR06-XR10: 8 A? XD26-XB26: 8 x 8 A relays, 2 x 5 A relays? XE10: 4 x 5 A relays? XR14: 4 x 8 A relays, 2 x 5 A relays
Electrical durability for 500 000 operating cycles	Utilization category DC-12: 24 V, 1.5 A? Utilization category DC-13: 24 V (L/R = 10 ms), 0.6 A? Utilization category AC-12: 230 V, 1.5 A? Utilization category AC-15: 230 V, 0.9 A
Minimum switching capacity	10 mA (at minimum voltage of 12 V)
Minimum load	12 V, 10 mA
Maximum rate	Off load: 10 Hz? At operating current: 0.1 Hz
Mechanical life	10,000,000 (operations)
Voltage for withstanding shocks	In accordance with IEC/EN 60947-1 and IEC/EN 60664-1: 4 kV
Response time	Make 10 ms? Release 5 ms
Built-in protections	Against short-circuits: None? Against overvoltages and overloads: None
Status indicator	On LCD screen for CD and XD

Digital / PWM solid state output

PWM solid state output*	CB12: O4? XD26: O4? O7	CD12-XD10-XB10: O4? CD20-XD26-XB26: O4? O7
* Only available with "FBD" programming language	* Only available with "FBD" programming language	
Breaking voltage	10.4? 30 V?	19.2? 30 V?
Nominal voltage	12-24 V?	24 V?
Nominal current	0.5 A	0.5 A
Max. breaking current	0,625 A	0,625 A
Voltage drop	≤ 2 V for I = 0.5 A (at state 1)	≤ 2 V for I = 0.5 A (at state 1)
Response time	Make ≤ 1 ms? Release ≤ 1 ms	Make ≤ 1 ms? Release ≤ 1 ms
Built-in protections	Against overloads and short-circuits: Yes? Against overvoltages (*) : Yes? Against inversions of power supply: Yes? (*) In the absence of a volt-free contact between the logic controller output and the load	Against overloads and short-circuits: Yes? Against overvoltages (*) : Yes? Against inversions of power supply: Yes? (*) In the absence of a volt-free contact between the logic controller output and the load
Min. load	1 mA	1 mA
Maximum incandescent load	0,2 A / 12 V? ? 0,1 A / 24 V?	0,1 A / 24 V?
Galvanic isolation	No	No
PWM frequency	14.11 Hz? 56.45 Hz? 112.90 Hz? 225.80 Hz? 451.59 Hz? 1806.37 Hz	14.11 Hz? 56.45 Hz? 112.90 Hz? 225.80 Hz? 451.59 Hz? 1806.37 Hz
PWM cyclic ratio	0? 100% (256 steps for CD, XD and 1024 steps for XA)	0? 100% (256 steps for CD, XD and 1024 steps for XA)
PWM accuracy at 120 Hz	< 5% (20%? 80%) load at 10 mA	< 5% (20%? 80%) load at 10 mA
PWM accuracy at 500 Hz	< 10% (20%? 80%) load at 10 mA	< 10% (20%? 80%) load at 10 mA
Status indicator	On LCD screen for XD	On LCD screen for CD and XD

Dimension Diagram : XR06

