



Fluke (U.K.) Ltd.

FLUKE

Combo Kit for Industrial applications



This new combo kit is based on the Industrial Fluke 87V multimeter. It includes the AC/DC current clamp i410 and the new C115 soft case. Save over 28% compared with the individual purchase price of the multimeter, current clamp and soft case.

The Fluke 87V has measurement functions, trouble-shooting features, resolution and accuracy to solve more problems on motor drives, in plant automation, power distribution and electro-mechanical equipment.

Fluke Current Clamps are the ideal tools to extend the current ranges of Fluke tools.

The new C115 Soft Carrying Case includes two padded pockets for protection of two test tools, such as the 87V DMM and the i410 Current Clamp and also a pouch for test leads and other accessories.

Model Name	Product Description	
Fluke 87V	True RMS Multimeter	
i410	AC/DC Current Clamp	
C115	Soft Meter and Accessory Case	

Fluke 83V and 87V True-rms Digital Multimeters Detailed Specifications

For all detailed specifications:

Accuracy is given as $\pm([\% \text{ of reading}] + [\text{number of least significant digits}])$ at 18 °C to 28 °C, with relative humidity up to 90 %, for a period of one year after calibration.

For Model 87 in the 4½-digit mode, multiply the number of least significant digits (counts) by 10. AC conversions are ac-coupled and valid from 3 % to 100 % of range. Model 87 is true-rms responding. AC crest factor can be up to 3 at full scale, 6 at half scale. For non-sinusoidal wave forms add $-(2 \% \text{ Rdg} + 2 \% \text{ full scale})$ typical, for a crest factor up to 3.



Fluke 87V ac voltage function specifications (true-rms)

Function	Range	Resolution	Accuracy					
			45 - 65 Hz	30 - 200 Hz	200 - 440 Hz	440 Hz - 1 kHz	1 - 5 kHz	5 - 20 kHz ¹
√ ^{2,4}	600.0 mV	0.1 mV	± (0.7 % + 4)	± (1.0 % + 4)	± (1.0 % + 4)	± (1.0 % + 4)	± (2.0 % + 4)	± (2.0 % + 20)
	6.000 V	0.001 V	± (0.7 % + 2)					
	60.00 V	0.01 V		± (0.7 % + 2)	± (2.0 % + 4) ³	unspecified		
	600.0 V	0.1 V						
	1000 V	1 V				unspecified	unspecified	
	Using low pass filter		± (0.7 % + 2)	± (1.0 % + 4)	+ 1 % + 4 -6 % - 4 ⁵	unspecified	unspecified	unspecified

¹ Below 10 % of range, add 6 counts.

² The Fluke 87V is a true-rms responding meter. When the input leads are shorted together in the ac functions, the meter may display a residual reading between 1 and 30 counts. A 30-count residual reading will cause only a 2-digit change for readings over 3 % of range. Using REL to offset this reading may produce a much larger constant error in later measurements.

³ Frequency range: 1 kHz to 2.5 kHz.

⁴ A residual reading of up to 13 digits with leads shorted, will not affect stated accuracy above 3 % of range.

⁵ Specification increases from -1 % at 200 Hz to -6 % at 440 Hz when filter is in use.

Fluke 83V ac voltage function specifications (average responding rms indicating)

Function	Range	Resolution	Accuracy		
			50 Hz - 60 Hz	30 Hz - 1 kHz	1 kHz - 5 kHz
√ ¹	600.0 mV	0.1 mV	± (0.5 % + 4)	± (1.0 % + 4)	± (2.0 % + 4)
	6.000 V	0.001 V	± (0.5 % + 2)	± (1.0 % + 4)	± (2.0 % + 4)
	60.00 V	0.01 V	± (0.5 % + 2)	± (1.0 % + 4)	± (2.0 % + 4)
	600.0 V	0.1 V	± (0.5 % + 2)	± (1.0 % + 4)	± (2.0 % + 4) ²
	1000 V	1 V	± (0.5 % + 2)	± (1.0 % + 4)	unspecified

¹ Below a reading of 200 counts, add 10 counts

² Frequency range: 1 kHz to 2.5 kHz

Fluke 83V and 87V Detailed Specifications cont.

DC voltage, resistance, and conductance function specifications

Function	Range	Resolution	Accuracy	
			Fluke 83V	Fluke 87V
\overline{V}	6.000 V	0.001 V	$\pm (0.1 \% + 1)$	$\pm (0.05 \% + 1)$
	60.00 V	0.01 V	$\pm (0.1 \% + 1)$	$\pm (0.05 \% + 1)$
	600.0 V	0.1 V	$\pm (0.1 \% + 1)$	$\pm (0.05 \% + 1)$
	1000 V	1 V	$\pm (0.1 \% + 1)$	$\pm (0.05 \% + 1)$
\overline{mV}	600.0 mV	0.1 mV	$\pm (0.3 \% + 1)$	$\pm (0.1 \% + 1)$
Ω	600.0 Ω	0.1 Ω	$\pm (0.4 \% + 2)^1$	$\pm (0.2 \% + 2)^1$
	6.000 k Ω	0.001 k Ω	$\pm (0.4 \% + 1)$	$\pm (0.2 \% + 1)$
	60.00 k Ω	0.01 k Ω	$\pm (0.4 \% + 1)$	$\pm (0.2 \% + 1)$
	600.0 k Ω	0.1 k Ω	$\pm (0.7 \% + 1)$	$\pm (0.6 \% + 1)$
	6.000 M Ω	0.001 M Ω	$\pm (0.7 \% + 1)$	$\pm (0.6 \% + 1)$
	50.00 M Ω	0.01 M Ω	$\pm (1.0 \% + 3)^2$	$\pm (1.0 \% + 3)^2$
nS	50.00 M Ω	0.01 M Ω	$\pm (1.0 \% + 3)^2$	$\pm (1.0 \% + 3)^2$
	60.00 nS	0.01 nS	$\pm (1.0 \% + 10)^1$	$\pm (1.0 \% + 10)^1$

¹ When using the REL Δ function to compensate for offsets

² Add 0.5 % of reading when measuring above 30 M Ω in the 50 M Ω range and 20 counts below 33 nS in the 60 nS range

Temperature specifications (87V only)

Temperature	Resolution	Accuracy ^{1, 2}
-200 °C to +1090 °C	0.1 °C	1 % + 10
-328 °F to +1994 °F	0.1 °F	1 % + 18

¹ Does not include error of the thermocouple probe.

² Accuracy specification assumes ambient temperature stable to ± 1 °C. For ambient temperature changes of ± 5 °C, rated accuracy applies after 1 hour.

Current function specifications

Function	Range	Resolution	Accuracy		Burden Voltage (typical)
			Model 83 ¹	Model 87 ^{2, 3}	
mA A~ (45 Hz to 2 kHz)	60.00 mA	0.01 mA	$\pm (1.2 \% + 2)^5$	$\pm (1.0 \% + 2)$	1.8 mV/mA
	400.0 mA ⁶	0.1 mA	$\pm (1.2 \% + 2)^5$	$\pm (1.0 \% + 2)$	1.8 mV/mA
	6.000 A	0.001 A	$\pm (1.2 \% + 2)^5$	$\pm (1.0 \% + 2)$	0.03 V/A
	10.00 A ⁴	0.01 A	$\pm (1.2 \% + 2)^5$	$\pm (1.0 \% + 2)$	0.03 V/A
mA A $\overline{\overline{}}$	60.00 mA	0.01 mA	$\pm (0.4 \% + 4)$	$\pm (0.2 \% + 4)$	1.8 mV/mA
	400.0 mA ⁶	0.1 mA	$\pm (0.4 \% + 2)$	$\pm (0.2 \% + 2)$	1.8 mV/mA
	6.000 A	0.001 A	$\pm (0.4 \% + 4)$	$\pm (0.2 \% + 4)$	0.03 V/A
	10.00 A ⁴	0.01 A	$\pm (0.4 \% + 2)$	$\pm (0.2 \% + 2)$	0.03 V/A
μ A~ (45 Hz to 2 kHz)	600.0 μ A	0.1 μ A	$\pm (1.2 \% + 2)^5$	$\pm (1.0 \% + 2)$	100 μ V/ μ A
	6000 μ A	1 μ A	$\pm (1.2 \% + 2)^5$	$\pm (1.0 \% + 2)$	100 μ V/ μ A
μ A $\overline{\overline{}}$	600.0 μ A	0.1 μ A	$\pm (0.4 \% + 4)$	$\pm (0.2 \% + 4)$	100 μ V/ μ A
	6000 μ A	1 μ A	$\pm (0.4 \% + 2)$	$\pm (0.2 \% + 2)$	100 μ V/ μ A

¹ AC conversion for Model 83 is ac coupled and calibrated to the rms value of a sine wave input.

² AC conversions for Model 87 are ac coupled, true rms responding, and valid from 3 % to 100 % of range.

³ Model 87 is a true rms responding meter. When the input leads are shorted together in the ac functions, the Meter may display a residual reading between 1 and 30 counts. A 30 count residual reading will cause only a 2 digit change for readings over 3 % of range. Using REL to offset this reading may produce a much larger constant error in later measurements.

⁴ Δ 10 A continuous up to 35 °C; < 20 minutes on, 5 minutes off at 35 °C to 55 °C. 20 A for 30 seconds maximum; > 10 A unspecified.

⁵ Below a reading of 200 counts, add 10 counts.

⁶ 400 mA continuous; 600 mA for 18 hours maximum.

Capacitance and diode function specifications

Function	Range	Resolution	Accuracy
— —	10.00 nF	0.01 nF	$\pm (1 \% + 2)^1$
	100.0 nF	0.1 nF	$\pm (1 \% + 2)^1$
	1.000 μ F	0.001 μ F	$\pm (1 \% + 2)$
	10.00 μ F	0.01 μ F	$\pm (1 \% + 2)$
	100.0 μ F	0.1 μ F	$\pm (1 \% + 2)$
	9999 μ F	1 μ F	$\pm (1 \% + 2)$
— +	3.000 V	0.001 V	$\pm (2 \% + 1)$

¹ With a film capacitor or better, using Relative mode to zero residual.

Frequency counter specifications

Function	Range	Resolution	Accuracy
Frequency (0.5 Hz to 200 kHz, pulse width > 2 μs)	199.99	0.01 Hz	± (0.005 % + 1)
	1999.9	0.1 Hz	± (0.005 % + 1)
	19.999 kHz	0.001 kHz	± (0.005 % + 1)
	199.99 kHz	0.01 kHz	± (0.005 % + 1)
	> 200 kHz	0.1 kHz	unspecified

Frequency counter sensitivity and trigger levels

Input Range ¹	Minimum Sensitivity (RMS Sine wave)		Approximate Trigger Level (DC Voltage Function)
	5 Hz - 20 kHz	0.5 Hz - 200 kHz	
600 mV dc	70 mV (to 400 Hz)	70 mV (to 400 Hz)	40 mV
600 mV ac	150 mV	150 mV	–
6 V	0.3 V	0.7 V	1.7 V
60 V	3 V	7 V (≤ 140 kHz)	4 V
600 V	30 V	70 V (≤ 14.0 kHz)	40 V
1000 V	100 V	700 V (≤ 1.4 kHz)	100 V
Duty Cycle Range	Accuracy		
0.0 to 99.9 %	Within ± (0.2 % per kHz + 0.1 %) for risetimes < 1 μs		

¹ Maximum input for specified accuracy = 10X Range or 1000 V.

Electrical characteristics of the terminals

Function	Overload Protection ¹	Input Impedance (nominal)	Common Mode Rejection Ratio (1 kΩ unbalance)		Normal Mode Rejection					
\bar{V}	1000 V rms	10 MΩ < 100 pF	> 120 dB at dc, 50 Hz or 60 Hz		> 60 dB at 50 Hz or 60 Hz					
\overline{mV}	1000 V rms	10 MΩ < 100 pF	> 120 dB at dc, 50 Hz or 60 Hz		> 60 dB at 50 Hz or 60 Hz					
\bar{V}	1000 V rms	10 MΩ < 100 pF (ac-coupled)	> 60 dB, dc to 60 Hz		Typical Short Circuit Current					
					Full Scale Voltage			Typical Short Circuit Current		
			To 6.0 MΩ	50 MΩ or 60 nS	600 Ω	6 k	60 k	600 k	6 MΩ	50 MΩ
Ω	1000 V rms	< 7.9 V dc	< 4.1 V dc	< 4.5 V dc	1 mA	100 μA	10 μA	1 μA	1 μA	0.5 μA
\rightarrow	1000 V rms	< 7.9 V dc	3.000 V dc		0.6 mA typical					

¹ 10⁶ V Hz maximum

MIN MAX recording specifications

Model	Nominal Response	Accuracy
83V	100 ms to 80 %	Specified accuracy ± 12 counts for changes > 200 ms in duration (± 40 counts in ac with beeper on)
87V	100 ms to 80 % (dc functions)	Specified accuracy ± 12 counts for changes > 200 ms in duration > 25 % of range
	120 ms to 80 % (ac functions)	Specified accuracy ± 40 counts for changes > 350 ms and inputs
	250 μs (peak) (Model 87 only) ¹	Specified accuracy ± 100 counts for changes > 250 μs in duration (add ± 100 counts for readings over 6000 counts) (add ± 100 counts for readings in Low Pass mode)

¹ For repetitive peaks: 1 ms for single events.

Fluke 83V and 87V General Specifications

Maximum voltage between any terminal and earth ground: 1000 V rms

Fuse protection for mA or μ A inputs: 44/100 A, 1000 V FAST Fuse

Fuse protection for A input: 11 A, 1000 V FAST Fuse

Display:

Digital: 6000 counts updates 4/sec; (Model 87V also has 19,999 counts in high-resolution mode)

Analog: 33 segments, updates 40/sec.

Frequency: 19,999 counts, updates 3/sec at > 10 Hz

Temperature: Operating: -20 °C to +55 °C; Storage: -40 °C to +60 °C

Altitude:

Operating: 2000 m

Storage: 10,000 m

Temperature coefficient: 0.05 x (specified accuracy)/ °C (< 18 °C or > 28 °C)

Electromagnetic compatibility: In an RF field of 3 V/m total accuracy = specified accuracy

Relative humidity: 0 % to 90 % (0 °C to 35 °C); 0 % to 70 % (35 °C to 55 °C)

Battery type: 9 V zinc, NEDA 1604 or 6F22 or 006P

Battery life: 400 hours typical with alkaline (with backlight off)

Vibration: Per MIL-PRF-28800 for a Class 2 instrument

Shock: 1 Meter drop per IEC 61010-1:2001

Size (HxWxL): 1.25 in x 3.41 in x 7.35 in (3.1 cm x 8.6 cm x 18.6 cm)

Size with holster and flex-stand: 2.06 in x 3.86 in x 7.93 in (5.2 cm x 9.8 cm x 20.1 cm)

Weight: 12.5 oz (355 g)

Weight with holster and flex-stand: 22.0 oz (624 g)

Safety: Complies with ANSI/ISA S82.01-2004, CSA 22.2 No. 1010.1:2004 to 1000 V Overvoltage Category III, IEC 664 to 600 V Overvoltage Category IV. UL listed to UL3111-1. Licensed by TÜV to EN61010-1.

Fluke. *Keeping your world
up and running.*

Fluke Corporation

PO Box 9090, Everett, WA USA 98206

Fluke Europe B.V.

PO Box 1186, 5602 BD
Eindhoven, The Netherlands

For more information call:

In the U.S.A. (800) 443-5853 or

Fax (425) 446-5116

In Europe/M-East/Africa (31 40) 2 675 200 or

Fax (31 40) 2 675 222

In Canada (800)-36-FLUKE or

Fax (905) 890-6866

From other countries +1 (425) 446-5500 or

Fax +1 (425) 446-5116

Web access: <http://www.fluke.com/>



Fluke (U.K.) Ltd.

FLUKE

i410 AC/DC Current Clamp

Specifications	
Measurement type	Hall sensor
Nominal current range	400 A, AC/DC
Continuous current range	1 A - 400 A AC/DC
Maximum Non-Destructive Current	400 A
Lowest measurable current	0.5 A
Basic Accuracy	3.5% + 0.5 A (% reading + floorspec)
Useable frequency	DC - 3 kHz
Output level(s)	1 mV/A
Zero error adjustment	Yes

Safety Specifications	
Safety	CAT III, 600 V
Maximum voltage	600 V

Mechanical & General Specifications	
Warranty	1 year
Battery Life	9 V, 60 h
Maximum conductor diameter	30 mm 2 x 25 mm



Fluke (U.K.) Ltd.

FLUKE

C115 Soft Carrying Case



- Includes two padded pockets for protection of two test tools, such as a digital multimeter and 60 Series IR thermometer and a pouch for test leads and other accessories.
- Durable polyester 600D case construction for long life.
- Compatible with Fluke 20, 70, 11X, 170 Series digital multimeters and other similar format test tools.
- One-year warranty.