







FIGURE 1

RECOMMENDED STRIP LENGTH

- ① CABLE USED WITHOUT SPACER
- ② CABLE USED WITH SPACER
3. SEE INSTRUCTION SHEET 408-9021
4. PARTS PACKAGED UNASSEMBLED
- ⑤ USE WITH PRO-CRIMPER 354940-1.
- ⑥ SPECIAL PACKAGING: INDIVIDUALLY PACKAGED
IN PRE-PRINTED BAG WITH SPECIAL GRAPHICS
- ⑦ BULK KIT PACKAGING 25 PIECES
- ⑧ BULK KIT PACKAGING 100 PIECES
- ⑨ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

9 OBSOLETE	JIS CABLE 3D-2V	△	5.41 [.213]	1.73 [.068]	58436-1	FIG 1	-	-	8-221132-9	1-222246-6	9-413636-3	3-5221128-1				
	BELDEN 9907, 89907 & RG-141/U	△	5.41 [.213]	1.73 [.068]	58436-1	FIG 1	-	-	9-221132-0	1-222246-6	9-413636-0	2-5221128-7				
	RG-179/U, 187/U	△	4.52 [.178]	1.73 [.068]	58436-3	FIG 1	227194-1	-	9-413658-0	1-222246-3	9-413636-2	2-5221128-3				
	RG-174/U, 188/U, 316/U	△	4.52 [.178]	1.73 [.068]	58436-3	FIG 1	227194-1	-	9-413658-0	1-222246-0	9-413636-2	2-5221128-1				
	RG-59/U, 59A/U, 59B/U	△	6.48 [.255]	1.73 [.068]	58436-1	FIG 1	-	227423-1	9-221132-1	222246-6	9-413636-1	4-5221128-8				
	BELDEN 9266	△	6.48 [.255]	1.73 [.068]	58436-1	FIG 1	-	-	9-221132-1	222246-2	9-413636-1	1-5221128-7				
	△ RG-62/U, 62A/U, 62B/U	△	6.48 [.255]	1.73 [.068]	58436-1	FIG 2	-	227423-1	9-221132-1	222246-4	9-413636-1	1-5221128-1				
	△ RG-59/U, 59A/U, 59B/U	△	6.48 [.255]	1.73 [.068]		FIG 1										
	△ RG-58/U, 58A/U, 58B/U, 58C/U	△	5.41 [.213]	1.73 [.068]	58436-1	FIG 1	-	-	9-221132-0	222246-2	9-413636-0	1-5221128-0				
	△ RG-62/U, 62A/U, 62B/U	△	6.48 [.255]	1.73 [.068]	58436-1	FIG 2	-	227423-1	9-221132-1	222246-4	9-413636-1	5221128-2				
△ RG-59/U, 59A/U, 59B/U	△	6.48 [.255]	1.73 [.068]	FIG 1												
	RG-58/U, 58A/U, 58B/U, 58C/U	△	5.41 [.213]	1.73 [.068]	58436-1	FIG 1	-	-	9-221132-0	222246-2	9-413636-0	5221128-1				
	FOR USE WITH CABLE	PACKAGING	FERRULE CONTACT		DIE SET 5	STRIP LENGTH 5	TUBING QTY=1	4	SPACER QTY=1	3	FERRULE QTY=1	2	CONTACT, PLUG QTY=1	1	PLUG ASSEMBLY QTY=1	PART NUMBER
			HEX CRIMP HEIGHTS													

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN J. ALCORTA 21APR2005 DOCKS				TE Connectivity			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWG J. HAVENER 21APR2005		NAME					
		Ø PLC ± —		PRODUCT SPEC		PLUG, COMMERCIAL BNC					
		1 PLC ± —		—							
		2 PLC ± 0.41 [016]		APPLICATION SPEC							
MATERIAL		ANGLES ± —		WEIGHT		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
—		FINISH		—		A1		00779	C=5221128	—	
				CUSTOMER DRAWING		SCALE		4:1	SHEET	1 of 1	REV A.3