

General Information

Extended Product Type:	SKT250-220-100
Product ID:	7TCA300180R0002
EAN:	5415022210286
Catalog Description:	NATURAL TIE 220N 250MM DISTRI PACK
Long Description:	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 250mm (9.842 Inches), Width of 4.8mm (0.189 Inches), Thickness of 1.3mm (0.051 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds)

Categories

Products » Low Voltage Products and Systems » Protection, Connection & Wire Management » Wire Management and Connectivity » Cable Ties

Ordering

EAN:	5415022210286
Minimum Order Quantity:	100 piece
Customs Tariff Number:	3926909995

Dimensions

Product Net Weight:	1.814 g
----------------------------	---------

Container Information

Package Level 1 Units:	100 piece
Package Level 1 Width:	130.048 mm
Package Level 1 Height:	70.104 mm
Package Level 1 Length:	370.078 mm
Package Level 2 Units:	12000 piece
Package Level 2 Width:	379.984 mm
Package Level 2 Height:	359.918 mm
Package Level 2 Length:	569.976 mm

Additional Information

Product Main Type:	GENERAL PURPOSE CABLE TIES AND ACCESSORIES
Product Name:	OTHER PLASTIC ITEM
UPC:	753554016552

Certificates and Declarations (Document Number)

Data Sheet, Technical Information: SKT250-220-100

Classifications

ETIM 6:	EC000046 - Cable tie
UNSPSC:	39121703

