

11 Electronics Wire Stripper



11 92 140

- ▶ for single, multiple and fine stranded cables with 0.1 up to 0.8 mm dia. with plastic or rubber insulation
- ▶ easy adjustment to the required diameter of solid or stranded wire with knurled screw and lock nut
- ▶ with opening spring
- ▶ the polish together with a fine film of oil offer the best possible rust protection - no circuit faults caused by peeling chrome from plated tools
- ▶ special tool steel, oil-hardened and tempered


Article-No.	EAN-Code	Head	Handles	Stripping capacities	g
Length mm	4003773-			ø mm	
11 92 140	016908	polished	with two-colour dual component handles	0.1 - 0.8	100

12 Automatic Insulation Strippers




12 11 180

- ▶ with replaceable blades of special steel for 4 and 6 positions resp. for different wire cross sections
- ▶ leaves wire undamaged; even multi-stranded conductors are stripped gently
- ▶ during stripping, the wire is held firmly by clamping jaws
- ▶ with length stop for constant stripping length during repetitive work
- ▶ a spring leads the stripper back to the starting position
- ▶ strong light-metal body



12 11 180



12 21 180

Article-No.	EAN-Code	Head	Handles	Stripping capacities				g
Length mm	4003773-			ø mm	mm ²	ø Inch	AWG	
12 11 180	000792	nickel plated	plastic handles	0.5/1.2/ 1.6/2.0		1/64 / 3/64 1/16 / 5/64		400
12 21 180	000815	nickel plated	plastic handles		0.5-0.75/1.0/ 1.5/2.5/4.0/6.0		20-18/17/ 15/13/11/9	400
12 19 180	022145	1 pair of spare blades for 12 11 180						
12 29 180	022152	1 pair of spare blades for 12 21 180						

