

# Fuseholders 5 x 20 mm



6.3A 250Vac (max fuse rating\*) T-55 to T+70 (ambient)

Maximum dissipation wattage: 1.5W

UL 94V2 UL file E92075 CSA file LR44770

These products comply with safety category PC2

\*Users should be aware of the de-rating factors published by specialist manufacturers of fuses


These fuseholders are fitted with combination (solder / 2.8) mid-body terminals  
It has not been possible to show both views here



**M520**  
Terminal Cover




**A0033 00**  
In-line 5 x 20 fuseholder  
Call factory for rating details



▶ TERMINAL	▶ BODY AND CAP	▶ PANEL HOLE
<p><b>T</b></p> <p>Solder</p>	<p><b>0332</b> Finger release</p> <p><b>0333</b> Tool release</p> <p><b>0340</b> Tool release</p> <p><b>0341</b> Tool release</p>	<p><b>RA</b></p> <p><b>RD</b></p>


## DIMENSIONS (mm)

### 0332 (T terminal shown)




Panel thickness 0.8-4.5mm

### 0333 (T terminal shown)




Panel thickness 0.8-4.5mm

### 0340 (T terminal shown)



Panel thickness 0.8-2.0mm

### 0341 (T terminal shown)



Panel thickness 0.8-4.5mm