

RGW6-T

ABB contact for United
Kingdom

General Information

Extended Product Type:	RGW6-T
Product ID:	1SNA510104R0000
EAN:	3472595101047
Catalog Description:	RGW6-T Ring Lug Terminal Block - Feed-Through with test sockets - Grey
Long Description:	RGW6-T Ring lug Terminal block - Feed-through with test sockets - Grey - 6mm ²

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Specific Terminal Blocks

Ordering

EAN:	3472595101047
Minimum Order Quantity:	40 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	11.0 mm
Product Net Height:	44.7 mm
Product Net Length:	52.15 mm
Product Net Depth:	52.2 mm
Product Net Weight:	19.00 g

Container Information

Package Level 1 Units:	40 piece
Package Level 1 Width:	171 mm
Package Level 1 Height:	84 mm
Package Level 1 Length:	97 mm
Package Level 1 Gross Weight:	0.88200 kg
Package Level 1 EAN:	3472595101047
Package Level 2 Units:	720 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	300 mm
Package Level 2 Length:	400 mm
Package Level 3 Units:	12960 piece

Environmental

Ambient Air Temperature:	Operation -40...+100 °C Storage -40...+100 °C
---------------------------------	--

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity-Main Circuit UL/CSA:	Stud / Rigid 1x 22-10 AWG

Additional Information

Ambient Temperature:	-25...+70 °C
Color:	Grey

Connection Type:	Stud
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10
Function:	Feed-through with test sockets
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Levels:	1
Power Loss:	1.3 W
Product Main Type:	RGW6-T
Product Name:	Terminal Block
Rated Cross-Section:	6 mm ²
Rated Current (I_n):	Main Circuit 41 A
Rated Short-time Withstand Current (I_{cw}):	for 1.0s 720 A
Rated Voltage (U_r):	800 V
RoHS Date:	20110721
Spacing:	11 mm
Sub-Function:	2 connections
Sub-Function 2:	1 feed-through circuit
Wire Stripping Length:	10.0 mm

Certificates and Declarations (Document Number)

CSA Certificate:	1SND168002A0200
cUL Certificate:	1SND168001A0201
Declaration of Conformity - CE:	1SND225158C1000
RoHS Information:	1SND230545F0200

Classifications

ETIM 4.0:	EC000897 - Feed-through terminal block
ETIM 5.0:	EC000897 - Feed-through terminal block

