


**RoHS**  
**2002/95/EC**  
**Compliant**

### SPECIFICATION

RATED VOLTAGE	480V
CURRENT	8A @ 40 °C
FREQUENCY	50 / 60 Hz
TEMPERATURE RANGE	-25 TO 85 °C
LEAKAGE CURRENT	6.6mA AT 250V 50Hz
TEST VOLTAGE	2kV DC
TERMINATIONS	5 WAY WAGO 236-505 SPRING CLAMP
TOTAL POWER	8.5W



### MINIMUM INSERTION LOSS

Frequency Hz	30k	100k	150k	300k	10M
Common Mode dB	20	62	76	>85	>85
Differential Mode dB		30	44	>54	>54