

2006

RELEASED FOR PUBLICATION




THIS DRAWING IS UNPUBLISHED.

ALL INTERNATIONAL RIGHTS RESERVED.

COPYRIGHT 2006

©

| LOC | DIST | REVISIONS<br>変更 |     |                           |         |     |      |
|-----|------|-----------------|-----|---------------------------|---------|-----|------|
| J   |      | P               | LTR | DESCRIPTION               | DATE    | DWN | APVD |
|     |      |                 | B   | REVISED PER ECR-10-010439 | 07JUN10 | HMR | T.M  |
|     |      |                 |     |                           |         |     |      |
|     |      |                 |     |                           |         |     |      |
|     |      |                 |     |                           |         |     |      |



1. APPLICATION TAB-HSG IS APPLIED TO THE PRODUCT OF 2.5mm PITCH OR MORE OF DYNAMIC DI000 SERIES. 2.0mm PITCH CANNOT BE USED.
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

1. DYNAMIC DI000シリーズの2.5mmピッチ以上のTAB-HSG製品に適用。
2. 0.0mmピッチの製品には使用不可。
2. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。

AS SHOWN:1903118-2

|                                                                                                                             |              |
|-----------------------------------------------------------------------------------------------------------------------------|--------------|
| △ COPPER ALLOY:<br>FINISH; CONTACT AREA Au 0.38μmMIN, OVER Ni 1.27μmMIN<br>銅合金:<br>下地; 全面ニッケルめっき1.27μm以上, 接点部; 金めっき0.38μm以上 | 1903118-2    |
| MATERIAL (材料)                                                                                                               | PART NO (型番) |

|                                                                                                                                                                                                                                                                                                                                                                |  |                                                                   |                                                                                                                                                             |                    |              |                                     |  |               |            |  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|--------------|-------------------------------------|--|---------------|------------|--|
| THIS DRAWING IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED FOR THE SPECIFIC PURPOSE AND NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT PERMISSION IN WRITING FROM TYCO ELECTRONICS CORPORATION. |  | WIRE RANGE<br>総合電線断面積<br>mm <sup>2</sup> 0.34~0.86                |                                                                                                                                                             | AWG#22~#18         |              | INSULATION DIA<br>被覆外径<br>φ1.4~φ2.2 |  |               |            |  |
| DIMENSIONS:<br>単位: 耗<br>mm                                                                                                                                                                                                                                                                                                                                     |  | DWN<br>M. MAEBASHI<br>11APR2006                                   | MATERIAL<br>材料                                                                                                                                              |                    | FINISH<br>仕上 |                                     |  |               |            |  |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br>一般公差 ±0.3, ±3°                                                                                                                                                                                                                                                                                                    |  | CHK<br>T. KUDO<br>11APR2006                                       |  <b>Tyco Electronics</b> Tyco Electronics Corporation<br>Kawasaki, Japan |                    |              |                                     |  |               |            |  |
| 0 PLC ±<br>1 PLC ±<br>2 PLC ±<br>3 PLC ±<br>4 PLC ±<br>ANGLES ±                                                                                                                                                                                                                                                                                                |  | APVD<br>D. MITSUGI<br>11APR2006                                   |                                                                                                                                                             |                    |              |                                     |  |               |            |  |
| PRODUCT SPEC<br>製品規格<br>108-78268                                                                                                                                                                                                                                                                                                                              |  | NAME<br>名称<br>DYNAMIC DI000 SERIES<br>TAB CONTACT Au, 2L-TYPE L/P |                                                                                                                                                             |                    |              |                                     |  |               |            |  |
| APPLICATION SPEC<br>取付適用規格<br>114-5377                                                                                                                                                                                                                                                                                                                         |  | SIZE<br>A4                                                        |                                                                                                                                                             | CAGE CODE<br>00779 |              | DRAWING NO<br>番号<br>C-1903118       |  | RESTRICTED TO |            |  |
| WEIGHT<br>0.086 g                                                                                                                                                                                                                                                                                                                                              |  | SCALE<br>尺度<br>7:1                                                |                                                                                                                                                             |                    |              |                                     |  |               | SHEET<br>1 |  |
| CUSTOMER DRAWING                                                                                                                                                                                                                                                                                                                                               |  | REV<br>B                                                          |                                                                                                                                                             |                    |              |                                     |  |               |            |  |