



# PLC-RPT- 12DC/21AU

Order No.: 2900317



PLC-INTERFACE, consisting of PLC-BPT.../21 basic terminal block with Push-in connection and plug-in miniature relay with multi-layer contact, for mounting on NS 35/7,5 DIN rail, 1 PDT, 12 V DC input voltage



| Commercial data          |   |
|--------------------------|---|
| EAN                      | 4 046356 507011  |
| Pack                     | 10  |
| Customs tariff           | 85364190  |
| Country of Origin        | DE  |
| Catalog page information | Page 83 (IF-2011)   |

### Product notes

WEEE/RoHS-compliant since: 17/11/2009



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

## Technical data

### Coil side

|                                   |         |
|-----------------------------------|---------|
| Nominal input voltage $U_N$       | 12 V DC |
| Nominal input current at $U_{IN}$ | 15.3 mA |
| Typical response time             | 5 ms    |
| Typical release time              | 8 ms    |

|                           |  |
|---------------------------|--|
| Operating voltage display | Yellow LED   |
| Protective circuit        | Protection against polarity reversal Polarity protection diode |
|                           | Free-wheeling diode Damping diode                              |

#### Contact side

|                                       |   |
|---------------------------------------|---|
| Contact type                          | Single contact, 1-PDT   |
| Contact material                      | AgSnO, hard gold-plated   |
| Maximum switching voltage             | 30 V AC   |
|                                       | 36 V DC   |
| Minimum switching voltage             | 100 mV (at 10 mA)   |
| Maximum inrush current                | 50 mA   |
| Min. switching current                | 1 mA (at 24 V)  |
| Limiting continuous current           | 50 mA   |
| Interrupting rating (ohmic load) max. | 1.2 W (at 24 V DC)  |
| Note                                  | <b>the following values are applicable if a gold layer is destroyed</b> |
| Maximum switching voltage             | 250 V AC/DC   |
| Minimum switching voltage             | 5 V (at 100 mA)   |
| Limiting continuous current           | 6 A   |
| Min. switching current                | 10 mA (at 12 V)   |
| Interrupting rating (ohmic load) max. | 140 W (at 24 V DC)  |
|                                       | 20 W (for 48 V DC)  |
|                                       | 18 W (for 60 V DC)  |
|                                       | 23 W (for 110 V DC)   |
|                                       | 40 W (for 220 V DC)   |
|                                       | 1500 VA (for 250 V AC)  |

#### General data

|  |                            |
|--|----------------------------|
| Width                                    | 6.2 mm                     |
| Height                                   | 80 mm                      |
| Depth                                    | 94 mm                      |
| Test voltage relay winding/relay contact | 4 kV AC (50 Hz, 1 min.)    |
| Ambient temperature (operation)          | -40 °C ... 60 °C           |
| Ambient temperature (storage/transport)  | -40 °C ... 85 °C           |
| Operating mode                           | 100% operating factor      |
| Mechanical service life                  | 2 x 10 <sup>7</sup> cycles |
| Inflammability class according to UL 94  | V0                         |

|                        |   |
|------------------------|---|
| Name                   | Standards/regulations                         |
| Standards/regulations  | IEC 60664                                     |
|                        | IEC 60664 A                                   |
|                        | DIN VDE 0110                                  |
|                        | DIN EN 50178/DIN VDE 0160 (in relevant parts) |
|                        | DIN EN 50178/VDE 0160                         |
|                        | IEC 60255/DIN VDE 0435 (in relevant parts)    |
| Pollution degree       | 3   |
| Surge voltage category | III   |
| Mounting position      | Any   |
| Assembly instructions  | In rows with zero spacing                     |

#### Connection data

|  |                      |
|--|----------------------|
| Connection method                      | Push-in connection   |
| Conductor cross section solid min.     | 0.14 mm <sup>2</sup> |
| Conductor cross section solid max.     | 2.5 mm <sup>2</sup>  |
| Conductor cross section stranded min.  | 0.14 mm <sup>2</sup> |
| Conductor cross section stranded max.  | 2.5 mm <sup>2</sup>  |
| Conductor cross section AWG/kcmil min. | 26                   |
| Conductor cross section AWG/kcmil max  | 14                   |
| Stripping length                       | 8 mm                 |

#### Certificates



Certification

CUL, CUL Listed, GL, UL, UL Listed

#### Accessories

| Item            | Designation                    | Description   |
|-----------------|--------------------------------|---|
| <b>Assembly</b> |                                |   |
| 0801762         | NS 35/ 7,5 CU UNPERF<br>2000MM | DIN rail, material: Copper, unperforated, height 7.5 mm, width 35 mm, length: 2 m |

|         |                              |  |
|---------|------------------------------|--|
| 0801733 | NS 35/ 7,5 PERF 2000MM       | DIN rail, material: steel galvanized and passivated with a thick layer, perforated, height 7.5 mm, width 35 mm, length: 2000 mm  |
| 0801681 | NS 35/ 7,5 UNPERF 2000MM     | DIN rail, material: Steel, unperforated, height 7.5 mm, width 35 mm, length: 2 m   |
| 0801377 | NS 35/ 7,5 V2A UNPERF 2000MM | DIN rail, Width: 35 mm, Height: 7.5 mm, Length: 2000 mm, Color: silver   |
| 1201756 | NS 35/15 AL UNPERF 2000MM    | DIN rail, deep drawn, high profile, unperforated, 1.5 mm thick, material: aluminum, height 15 mm, width 35 mm, length 2000 mm  |
| 1201895 | NS 35/15 CU UNPERF 2000MM    | DIN rail, material: Copper, unperforated, 1.5 mm thick, height 15 mm, width 35 mm, length: 2 m   |
| 1201730 | NS 35/15 PERF 2000MM         | DIN rail, material: steel galvanized and passivated with a thick layer, perforated, height 15 mm, width 35 mm, length: 2000 mm   |
| 1201714 | NS 35/15 UNPERF 2000MM       | DIN rail, material: Steel, unperforated, height 15 mm, width 35 mm, length: 2 m  |
| 1201798 | NS 35/15-2,3 UNPERF 2000MM   | DIN rail, material: Steel, unperforated, 2.3 mm thick, height 15 mm, width 35 mm, length: 2 m  |
| 2966841 | PLC-ATP BK                   | Separating plate, 2 mm thick, required at the start and end of a PLC terminal strip. Furthermore, it is used for: visual separation of groups, safe isolation of different voltages of neighboring PLC relays in acc. with DIN VDE 0106-101, isolation |

#### Bridges

|         |                 |  |
|---------|-----------------|--|
| 2966812 | FBST 6-PLC BU   | Single plug-in bridge, Length: 6 mm, Number of positions: 2, Color: blue |
| 2966825 | FBST 6-PLC GY   | Single plug-in bridge, Length: 6 mm, Number of positions: 2, Color: gray |
| 2966236 | FBST 6-PLC RD   | Single plug-in bridge, Length: 6 mm, Number of positions: 2, Color: red  |
| 2967688 | FBST 8-PLC GY   | Single plug-in bridge, Length: 8 mm, Number of positions: 2, Color: gray |
| 2966692 | FBST 500-PLC BU | Continuous plug-in bridge, Length: 500 mm, Color: blue                   |
| 2966838 | FBST 500-PLC GY | Continuous plug-in bridge, Length: 500 mm, Color: gray                   |
| 2966786 | FBST 500-PLC RD | Continuous plug-in bridge, Length: 500 mm, Color: red                    |

#### General

|         |                |   |
|---------|----------------|---|
| 2966508 | PLC-ESK GY     | Power terminal block, for the input of up to four potentials, for mounting on NS 35/7.5   |
| 2296087 | PLC-V8/D15B/IN | V8-INPUT adapter for eight 6.2 mm PLC interfaces (1 PDT, etc./ see "Additional Products"). 15-pin D-SUB female connector, control logic: Positive switching |
| 2296074 | PLC-V8/D15S/IN | V8-INPUT adapter for eight 6.2 mm PLC interfaces (1 PDT, etc./ see "Additional Products"). 15-pin D-SUB male connector, control logic: Positive switching   |

|         |                   |   |
|---------|-------------------|---|
| 2296553 | PLC-V8/FLK14/IN   | V8L-INPUT adapter for eight 6.2 mm PLC interfaces (1 PDT, etc./see "Supplementary Products"). 14-pos. flat-ribbon cable connection for the PLC system cabling, control logic: Plus switching  |
| 2304115 | PLC-V8/FLK14/IN/M | V8L-INPUT adapter for eight 6.2 mm PLC interfaces (1 PDT, etc./see "Supplementary Products"). 14-pos. flat-ribbon cable connection for the PLC system cabling, control logic: Minus switching |

### Marking

|         |                        |   |
|---------|------------------------|---|
| 1051016 | ZB 6,LGS:FORTL.ZAHLEN  | Zack marker strip, Strip, white, Labeled, Can be labeled with: Plotter, Printed horizontally: Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500, Mounting type: Snap into tall marker groove, For terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm |
| 5060935 | ZB 6/WH-100:UNBEDRUCKT | Zack marker strip, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm  |
| 1051003 | ZB 6:UNBEDRUCKT        | Zack marker strip, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 6.2 mm, Lettering field: 6.15 x 10.5 mm  |

### Relay

|         |                   |  |
|---------|-------------------|--|
| 2961163 | REL-MR- 12DC/21AU | Pluggable miniature relays, with multi-layer contact, 1 PDT, input voltage 12 V DC |
|---------|-------------------|--|

### Tools

|         |               |   |
|---------|---------------|---|
| 1204517 | SZF 1-0,6X3,5 | Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip |
|---------|---------------|---|

## Drawings

### Circuit diagram

