


US Power Supply Cord with C7P Plug, Straight



Description

- 1 Function :
- Power Cord ,
- Protection class II ,
- Pin temperature 70 °C ,
- polarized
- custom specific versions on request

Technical Data

Ratings UL/CSA	7 A / 125 VAC; 50/60Hz	appliance inlet/-outlet	C7p acc. to IEC 60320-1
Dielectric Strength	> 2 kVDC between L-N > 2 kVAC between L/N-PE (1 min/50Hz)		UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 2.5A, Protection Class II
Allowable Operation Temp.	-25 °C to 70 °C		
IP-Protection	from front side IP 20 acc. to IEC 60529		
Insulation cover	Suitable for appliances with protection class II acc. to IEC 61140		
Terminal	moulded		
Material: Housing	PVC, black		

All Variants

Connector		cable				Plug					Order Number
Type	V-Lock	Cord Type	Conductor cross section	Length [m]	Color	Type	Country	Standard	Style	Index	
C7p		SVT 2x18 AWG	2 x 18 AWG	2.5	black	North America	USA	NEMA 1-15 pol.	straight	-	6052.0047

Most Popular.

Availability for all products can be searched real-time:<http://www.schurter.com/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 50 Pcs

Mating Inlets/Plugs

Category / Description



Appliance Inlet Overview complete

IEC Appliance Inlet C8 polarized, Screw-on Mounting, Front Side, Solder, Quick Connect or PCB Terminal	2577
IEC Appliance Inlet C8 polarized, Snap-in Mounting, Front Side, Solder, Quick Connect or PCB Terminal	2579

[Appliance Inlet further types to 6052.0047](#)



Power Entry Module Overview complete

IEC Appliance Inlet C8 polarized with Line Switch 1-pole	CMF2, CMF5
--	------------

[Power Entry Module further types to 6052.0047](#)