

**General Information**

<b>Extended Product Type:</b>	SKT140-180X-100
<b>Product ID:</b>	7TCA300140R0000
<b>EAN:</b>	5415022210064
<b>Catalog Description:</b>	UV BLACK TIE 180N 140MM DISTRI PACK
<b>Long Description:</b>	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 140mm (5.51 Inches), Width of 3.6mm (0.142 Inches), Thickness of 1.2mm (0.047 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds)

**Categories**

Products » Low Voltage Products and Systems » Protection, Connection & Wire Management » Wire Management and Connectivity » Cable Ties

**Ordering**

<b>EAN:</b>	5415022210064
<b>Minimum Order Quantity:</b>	100 piece
<b>Customs Tariff Number:</b>	3926909995

**Dimensions**

<b>Product Net Weight:</b>	0.816 g
----------------------------	---------

**Container Information**

<b>Package Level 1 Units:</b>	100 piece
<b>Package Level 1 Width:</b>	109.982 mm
<b>Package Level 1 Height:</b>	20.066 mm
<b>Package Level 1 Length:</b>	270.002 mm
<b>Package Level 2 Units:</b>	30000 piece
<b>Package Level 2 Width:</b>	379.984 mm
<b>Package Level 2 Height:</b>	359.918 mm
<b>Package Level 2 Length:</b>	569.976 mm

**Additional Information**

<b>Product Main Type:</b>	GENERAL PURPOSE CABLE TIES AND ACCESSORIES
<b>Product Name:</b>	OTHER PLASTIC ITEM
<b>UPC:</b>	753554016330

**Certificates and Declarations (Document Number)**

<b>Data Sheet, Technical Information:</b>	SKT140-180X-100
---	-----------------

**Classifications**

<b>ETIM 6:</b>	EC000046 - Cable tie
<b>UNSPSC:</b>	39121703

