

REVISION AY


DO NOT SCALE
FROM THIS PRINT


TABLE 1

TERMINAL STYLE	TERMINAL/BODY SPECIFICATION				FIG.	SHEET
	TS: SINGLE	TS BODY	TD: DOUBLE	TD BODY		
-AA	T-1R5-X	SEE NOTE 7	T-1R5-X	SEE NOTE 6	1	2
-A	T-1R0-X	SEE NOTE 7	T-1R0-X	SEE NOTE 6	2	2
-A-1	T-1R7-1-X	SEE NOTE 7	T-1R7-1-X	SEE NOTE 6	3	2
-A-2	T-1R7-2-X	SEE NOTE 7	T-1R7-2-X	SEE NOTE 6	4	2
-B	T-1R1-X	SEE NOTE 10	T-1R1-X	SEE NOTE 6	5	2
-B-2	T-1R8-2-X	SEE NOTE 7	T-1R8-2-X	SEE NOTE 6	7	2
-C	T-1R2-X	SEE NOTE 7	T-1R2-X	SEE NOTE 6	8	2
-C-1	T-1R9-1-X	SEE NOTE 7	T-1R9-1-X	SEE NOTE 6	9	2
-C-2	T-1R9-2-X	SEE NOTE 7	T-1R9-2-X	SEE NOTE 6	10	2
-D-1-1	T-1S4-1-1-X	SEE NOTE 7	T-1S4-1-1-X	SEE NOTE 6	11	3
-D-1-2	T-1S4-1-2-X	SEE NOTE 7	T-1S4-1-2-X	SEE NOTE 6	12	3
-E	T-1R12-X	SEE NOTE 7	N/A		17	3
**F	T-1S5-X	SEE NOTE 7	T-1S5-X	SEE NOTE 6	18	3
-G-1	T-1R5-1-X	SEE NOTE 7	T-1R5-1-X	SEE NOTE 6	19	3
-J	S-1P1-X	SEE NOTE 8	S-1P1-X	DSB-36	21	4
-K	T-1R12-X	SEE NOTE 7	T-1R12-X	SEE NOTE 6	22	4
-L-1	S-1W1-1-X	SEE NOTE 8	S-1W1-1-X	DSB-36	23	4
-L-2	S-1W1-2-X	SEE NOTE 8	S-1W1-2-X	DSB-36	24	4
-L-3	S-1W1-3-X	SEE NOTE 8	S-1W1-3-X	DSB-36	25	4
-N	T-1R5-1-X	SEE NOTE 7	N/A		27	4
-Q-3 *	S-1W1-3-X	SEE NOTE 7	N/A		29	4

**NOT AVAILABLE WITH -G PLATING

N/A = NOT AVAILABLE * STYLE -Q-3 AVAILABLE ONLY AS A COMPONENT
OF CSP/25 CABLE ASSEMBLIES.

DIMENSIONS ARE IN INCHES			TOLERANCES ARE:		TITLE: TERMINAL STRIP ASSEMBLY	DWG NO: TX-1XX-X-X SHEET 1 OF 4
ONE PLACE DECIMALS ±	TWO PLACE DECIMALS ±	THREE PLACE DECIMALS ±	FOUR PLACE DECIMALS ±	ANGLES ± 2°		



BODY SPEC.	LEAD STYLE	TUBE	PLUG
TS	A-1, A-2, A, AA, B, C, H, G-1	PT-1-24-01-24	TP-24
	J	PT-1-24-01-23	TP-12
	D-1-2	PT-1-24-02-03	TP-24
	D-1-1	PT-1-24-10-03	TP-03
TD	A-1	PT-1-24-05-17	TP-07
	A-2	PT-1-24-02-46	
	A, AA	PT-1-24-01-22	TP-03
	J	PT-1-24-01-14	

AY

CRITICAL DIMENSION INSPECTION TABLE	
ASSEMBLY OPERATION	IN-PROCESS INSPECTION
FILL	C3, C4
RA	C5
MULTI CUT	C1
CPCS INTENTIONALLY DELETED: C2	

NOTE:

- SEE COMPONENT PRINT FOR MAXIMUM ALLOWABLE BOW.
- MINIMUM PUSHOUT FORCE = 5 LBS.
- MAXIMUM ALLOWABLE TOE IN/OUT OF TERMINALS = ± 2°.
- MAX ALLOWABLE FLASH AFTER REMOVAL OF CROSS BARS: .005 [.13]
- ⊕ REPRESENTS A CRITICAL DIMENSION.
- USE DSB-36 AND FILL WITH COUNTERBORE DOWN.
- USE TBS-32 AND FILL WITH COUNTERBORE UP.
- USE SSB-XX AND FILL WITH COUNTERBORE UP.
- FOR LEAD STYLES PACKAGED IN TUBES: PACKAGE -05 THRU -36 POSITIONS IN TUBES; LAYER PACKAGE SMALLER POSITIONS.
- USE SSB-XX AND FILL WITH COUNTERBORE DOWN.
- FOR 1 POSITION TD ASSEMBLY, USE A TS-132 AND CUT TO A 2 POSITION.

MATERIAL: INSULATOR: GLASS FILLED POLYESTER COLOR: BLACK TERMINAL: BRASS, EXCEPT STYLE G IS PHOSPHOR BRONZE	 520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150 PHONE (812) 944-6733 P.O. BOX 1147 CODE 55322	
	MADE BY: L.W. 12/05/84	TX-1XX-X-X SHEET 1 OF 4

PLOT SCALE: 1=.1

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.