

Master cable - SAC-12P-10,0-PUR/M12FS MC - 1530799


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Master cable, 12-position, PUR/PVC, Black RAL 9005, free cable end, on Socket straight M12, A-coded, Cable length: 10 m



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 024471
Weight per Piece (excluding packing)	461.2 g
Custom tariff number	85444290
Country of origin	Germany

Technical data

General

Rated voltage	30 V
Number of positions	12
Inflammability class according to UL 94	HB

Ambient conditions

Degree of protection	IP68
----------------------	------

Insulation material

Contact material	CuSn
Contact surface material	Au

Classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801

Master cable - SAC-12P-10,0-PUR/M12FS MC - 1530799

Classifications

eCl@ss

eCl@ss 6.0	27061801
eCl@ss 7.0	27061801

ETIM

ETIM 2.0	EC000830
ETIM 3.0	EC001855
ETIM 4.0	EC001855
ETIM 5.0	EC001855

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Drawings

Master cable - SAC-12P-10,0-PUR/M12FS MC - 1530799

Circuit diagram

