

D

C

B



A

D

C

B

A



796640-3 AS SHOWN

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	F8	REVISED PER ECO-11-004587		11MAR2011	RK	HMR	

13	TIN	7	9	MARK 4 TO 1	20.00	4	5-796640-4	
	TIN	7	9	MARK 3 TO 1	15.00	3	5-796640-3	
	TIN	7	9	MARK 1 TO 3	15.00	3	5-796640-2	
3	12	TIN	7	9	MARK 1 TO 3	15.00	3	5-796640-1
	13	TIN	7	9	MARK 1 TO 4	20.00	4	5-796640-0
	13	TIN	7	9	MARK 15 TO 28	70.00	14	4-796640-9
13	TIN	7	9	MARK 13 TO 24	60.00	12	4-796640-8	
	13	TIN	7	9	MARK 1 TO 14	70.00	14	4-796640-7
	13	TIN	8	9	MARK 1 TO 12	60.00	12	4-796640-6
13	TIN	8	9	MARK 1 TO 7	35.00	7	4-796640-5	
	13	TIN	8	9	MARK 1 TO 5	25.00	5	4-796640-4
	13	TIN	8	9	MARK 11 TO 15	25.00	5	4-796640-3
CE	TIN	8	9	MARK 11 TO 15	25.00	5	4-796640-3	
	TIN	-	-	DETAIL S	35.00	7	4-796640-2	
	TIN	7	9	MARK 1 TO 3	15.00	3	4-796640-1	
TIN	-	-	10	20.00	4	4-796640-0		
	TIN	7	9	DETAIL P	20.00	4	3-796640-9	
	TIN	7	9	MARK 1 TO 8	40.00	8	3-796640-8	
TIN	7	9	MARK 37 TO 54	90.00	18	3-796640-7		
	TIN	7	9	MARK 19 TO 36	90.00	18	3-796640-6	
	TIN	7	9	MARK 1 TO 18	90.00	18	3-796640-5	
TIN	8	9	MARK 1 TO 10	50.00	10	3-796640-4		
	TIN	8	9	MARK 1 TO 8	40.00	8	3-796640-3	
	TIN	7	-	DETAIL N	30.00	6	3-796640-0	
TIN	7	9	MARK 1 TO 6	30.00	6	2-796640-9		
	TIN	-	-	125.00	25	2-796640-5		
	TIN	-	-	120.00	24	2-796640-4		
TIN	-	-	115.00	23	2-796640-3			
	TIN	-	-	110.00	22	2-796640-2		
	TIN	-	-	105.00	21	2-796640-1		
TIN	-	-	100.00	20	2-796640-0			
	TIN	-	-	95.00	19	1-796640-9		
	TIN	-	-	90.00	18	1-796640-8		
TIN	-	-	85.00	17	1-796640-7			
	TIN	-	-	80.00	16	1-796640-6		
	TIN	-	-	75.00	15	1-796640-5		
TIN	-	-	70.00	14	1-796640-4			
	TIN	-	-	65.00	13	1-796640-3		
	TIN	-	-	60.00	12	1-796640-2		
TIN	-	-	55.00	11	1-796640-1			
	TIN	-	-	50.00	10	1-796640-0		
	TIN	-	-	45.00	9	796640-9		
TIN	-	-	40.00	8	796640-8			
	TIN	-	-	35.00	7	796640-7		
	TIN	-	-	30.00	6	796640-6		
TIN	-	-	25.00	5	796640-5			
	TIN	-	-	20.00	4	796640-4		
	TIN	-	-	15.00	3	796640-3		
TIN	-	-	10.00	2	796640-2			
	TERMINAL PLATING	MARKING	SPECIAL	L	NO OF POSN	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S. WELDON 18OCT2000

CHK D. BIEVENOUR 18OCT2000

APVD D. BIEVENOUR 18OCT2000

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TERMINAL BLOCK, PLUG, STACKING

5.00mm PITCH

A200779


C-796640

SCALE 4:1


SHEET 1 OF 2

REV F8


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
-	-	SEE SHEET 1	-	-	-	




DETAIL N




DETAIL S




DETAIL P




DETAIL T




DETAIL U



DETAIL V



DETAIL W



1 MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: GREEN.
CLAMP: BRASS, NICKEL PLATED.
DOUBLE SIDE CONTACT SPRING: PHOSPHOR BRONZE, PLATING: SEE TABLE.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2. END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING.

3. WIRE SIZE RANGE: 12-30 AWG.

4. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.FILE N° E60677.

5. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.

6 NOT CUMULATIVE TOLERANCE

7 INK MARKING: BLACK COLOR.

8 INK MARKING: WHITE COLOR.

9 NUMERICAL SEQUENCE: FROM LEFT TO RIGHT, WIRE ENTRY SIDE.

10 RETENTION LATCHES REMOVED

11. BUCHANAN LOGO TO APPEAR ON HOUSING, LOCATION OPTIONAL WHERE SPACE PERMITS.

12 WIRE ENTRY CLOSED.

13 PRELIMINARY - NOT FOR PRODUCTION.

14 NUMERICAL SEQUENCE: FROM RIGHT TO LEFT, WIRE ENTRY SIDE.

13	TIN	-	DETAIL W, NO LATCH KEY POSN 1,4,7	35.00	7	6-796640-1
13	TIN	7 14	DETAIL V	60.00	12	6-796640-0
13	GOLD FLASH	-	-	35.00	7	5-796640-9
	TIN	7	DETAIL U	10.00	2	5-796640-8
	TIN	7	DETAIL T	30.00	6	5-796640-7
13	TIN	7 9	MARK 13 TO 24	60.00	12	5-796640-6
13	TIN	7 9	MARK 25 TO 38	70.00	14	5-796640-5
	TERMINAL PLATING	MARKING	SPECIAL	L	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON	18OCT2000	 TE Connectivity		
DIMENSIONS:		CHK D. BIEVENOUR	18OCT2000			
mm		APVD D. BIEVENOUR	18OCT2000			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC				
0 PLC ±		APPLICATION SPEC		NAME TERMINAL BLOCK, PLUG, STACKING 5.00mm PITCH		
1 PLC ±0.3				SIZE	CAGE CODE	DRAWING NO
2 PLC ±0.25				A2	00779	C-796640
3 PLC ±				RESTRICTED TO		
4 PLC ±				-		
ANGLES ±2		WEIGHT	-	SCALE 4:1		
FINISH		CUSTOMER DRAWING		SHEET 2 OF 2		
-				REV F8		