

VOLTAGE TESTER | TESTBOY 110 | Contact-less voltage tester

The new Testboy 110 is a further development of the proven Testboy 100. Due to the fact that it is so easy to operate and the diversity of options for its use in a wide variety of applications it should be part of the basic equipment of both DIY enthusiasts and professional electricians alike.

Made of impact resistant and unbreakable ABS plastic, the housing is suitable for use in tough conditions. An integrated LED torch is a great help in quickly and reliably finding defective cables.



Your advantages:

- | 5 years manufacturer's warranty
- | TÜV / GS tested and approved
- | IEC/EN 61010-1, DIN VDE 0411

The contact-less Testboy voltage tester can, for example, detect live wires in splices, cable drums, socket outlets and switches. A defective lamp in a chain of lights can be localised within seconds. An invisible cable breakage in an extension lead is indicated to within a tolerance of just a few millimetres.

In contrast to the inductive method of measurement, the capacitive technique requires no current flow.

Thus interruptions can be indicated rapidly and precisely within a centimetre.

The Testboy 110 was specially developed for use in installation tasks. Being so easy to handle makes it particularly suitable for use in areas where accessibility is restricted.

VOLTAGE TESTER | SPECIFICATION

Technical Details	Testboy 110
Display	optical
Measurement Range	12V to 1000V AC
Power Supply	2x 1,5V
Protection	IP 44
Overload Category	CAT III 1000V
TÜV/GS	IEC/EN 61010-1
Dimension	160 x 25 mm
Weight	45 g
Integrated LED-torch Lamp	yes
Colour	red, other colours on request
Scope of Delivery	1 x operating instructions 2 x battery type AAA LR03

12
-1000V
AC


CAPACITIVE


CONTACT-LESS

4mm
RESPONSE


OPTICAL



3
YEARS
WARRANTY