

Interface module - FLKM-D25 SUB/B/KDS3-MT/TU810/P - 2304539

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




VARIOFACE module, with knife disconnect terminal blocks for: -S800 I/O input module, module width: 126.5 mm

Why buy this product

- Eight positive terminal blocks with knife disconnection (TU810/P)
- Eight negative terminal blocks with knife disconnection (TU810)
- One positive and negative terminal block with knife disconnection per channel (TU830)



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 949129
Weight per Piece (excluding packing)	269.84 g
Custom tariff number	85369010
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	126.5 mm
Height	90 mm
Depth	61 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	< 50 V AC
	60 V DC
Max. perm. current (per branch)	2 A
Max. permissible current (separate power supply)	4 A (8 A L1+/L2+)

Interface module - FLKM-D25 SUB/B/KDS3-MT/TU810/P - 2304539

Technical data

General

Number of positions	25
Status display	No
Mounting position	any
Assembly instructions	In rows with zero spacing
Degree of protection	IP00
Standards/regulations	DIN EN 50178
	IEC 60664
	IEC 62103
Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (Functional insulation)
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	Field level
Connection method	Screw connection with disconnect knife
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

Connection data for connection 2

Connection name	Controller level
Connection method	D-SUB socket strip
Number of positions	25

Supported controller

Controller	ABB S800 I/O
- suitable I/O card	DI810
	DI811
	DI830
	DI831
	DI840
	DO814
	AI810
	AI820
	AI845
	AO820

Interface module - FLKM-D25 SUB/B/KDS3-MT/TU810/P - 2304539

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152

ETIM


ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Drawings

Circuit diagram



FLKM-D25 SUB/B/KDS3-MT/TU810/P connection scheme