




Mating Height Draw.



Specifications:

Current Rating: 1.5A AC/DC

Voltage Rating: 230V AC/DC

Contact Resistance: 20m ohm. Max.

Insulation Resistance: 1000M ohm. Min.

Withstanding Voltage: AC 500V AC/minute

Operating Temperature Range: -40°C ~ +105°C

Material and Finish

Insulator: High Temp. Plastic (UL94V-0)

Contact material: Phosphor Bronze

Finish: Tin Plated

How to Order

TMM-X-X-XX-X

Type

- 1-IDC Male
- 2-IDC Plug
- 3-DIP Male Straight
- 4-DIP Female Straight
- 5-DIP Female R/A
- 6-SMT Female Straight

Packaging


- 1 - Tape & Reel with vacuum cap
- 2 - Tube
- 3 - Bag
- 4 - Tape & Reel without vacuum cap

Number of Positions

- 04, 06, 08, 10, 12, 14,
- 16, 18, 20, 22, 24 or 26

Locking System

- 0-without lock
- L-with lock



PCB Layout

Circuits	Dimension		Circuits	Dimension		Circuits	Dimension	
	A	B		A	B		A	B
4	7.20	2.54	12	17.36	12.70	20	27.52	22.86
6	9.74	5.08	14	19.90	15.24	22	30.06	25.40
8	12.28	7.62	16	22.44	17.78	24	32.60	27.94
10	14.82	10.16	18	24.98	20.32	26	35.14	30.48



TOLERANCE (mm)	APPROVALS	DATE	TITLE		AMPHENOL	
X. ±0.3	DRAWN Stephane	2009/10/07	TMM Sereis Dip Type Male		Amphenol European Design Center	
X.X ±0.2	CHECKED Rob	2009/10/07				
X.XX ±0.15	APPROVED Rob	2009/10/07				
UNLESS OTHERWISE SPECIFIED	UNIT:	mm	SIZE: A4	DRAWING N°	TMM-3-0-XX-X	REV. D
					Scale N.A.	Sheet 1 of 1