




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
CM	00	R		REVISED PER ECO-05-001606	21JULY05	KW SR




1. PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
- 2



CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN LEAD ON SOLDER TAIL END.
- 3

CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5

CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.



3-DIMENSIONAL MODEL
NTS



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 [.062] THICK P.C. BOARD

PHOSPHOR BRONZE, GOLD 3	NYLON,UL94V-2,NATURAL	350759-5
PHOSPHOR BRONZE, PRE-TIN	NYLON,UL94V-2,NATURAL	350759-4
PHOSPHOR BRONZE, GOLD 3	NYLON,UL94V-2,NATURAL	350759-3
CONTACT MATERIAL AND FINISH	HOUSING MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 21JULY2005	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608
DIMENSIONS: mm [INCHES]		CHK S. RIDGILL 21JULY2005	
⊕ —	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S. RIDGILL 21JULY2005	NAME SOCKET HEADER ASSEMBLY, 2 CIRCUIT UNIVERSAL MATE-N-LOK(TM)
	0 PLC ± —	PRODUCT SPEC	
	1 PLC ± —	APPLICATION SPEC	
	2 PLC ± 0.13 [.005]	—	
MATERIAL SEE TABLE	3 PLC ± —	WEIGHT	SIZE A1
	4 PLC ± —	—	CAGE CODE 00779
ANGLES FINISH SEE TABLE		RESTRICTED TO	—
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 of 1
		REV R	

