



RE1001-LFDS

- Adaptable basic board
- Epoxy fibre-glass FR4 1.50 mm
- Double sided 35 µm Cu
- Without holes
- Hot air leveling (HAL-leadfree)
- Size 100 x 200 mm



RE1001-LFDS

- Adaptacks-Basisplatine
- Epoxydglashartgewebe FR4 1,50 mm
- Zweiseitig 35 µm Cu
- Keine Bohrungen
- Heißverzinnt (HAL-leadfree)
- Größe 100 x 200 mm



RE1001-LFDS

- Adaptacks-Platine de base
- Fibre de verre époxyde FR4 1,50 mm
- Double face 35 µm Cu
- Sans trous
- Étamée à chaud (HAL-leadfree)
- Dimensions 100 x 200 mm



RE1001-LFDS

- Adaptacks-Placa básica
- Fibra de vidrio epoxídica FR4 1,50 mm
- Por dos lados 35 µm de Cu
- Sin agujeros
- Estañado en caliente (HAL-leadfree)
- Tamaño 100 x 200 mm