

WIRING DIAGRAM	LOCKNUT LN-SS12	SPECIFICATIONS																		
OUTPUT: AN6X	M12x1 .669 17.0 .768 19.5 .157 4.0	<table><tr><td colspan="2">SPECIFICATIONS</td></tr><tr><td>RATED OPERATING DISTANCE</td><td>4mm =.158"</td></tr><tr><td>MOUNTING MODE</td><td>FLUSH</td></tr><tr><td>MIN. REPEAT ACCURACY</td><td>≤ 2%</td></tr><tr><td>TEMPERATURE DRIFT</td><td>≤±10% ≤±15%, ≤ -25°C v ≥ +70°C</td></tr><tr><td>HYSTERESIS (SWITCHING DISTANCE)</td><td>3-15%</td></tr><tr><td>OPERATING TEMPERATURE</td><td>-30°C to +85°C (-22°F to +185°F)</td></tr><tr><td>RATED OPERATIONAL VOLTAGE</td><td>10-30 VDC</td></tr><tr><td>MAX. RIPPLE</td><td>≤10%</td></tr></table>	SPECIFICATIONS		RATED OPERATING DISTANCE	4mm =.158"	MOUNTING MODE	FLUSH	MIN. REPEAT ACCURACY	≤ 2%	TEMPERATURE DRIFT	≤±10% ≤±15%, ≤ -25°C v ≥ +70°C	HYSTERESIS (SWITCHING DISTANCE)	3-15%	OPERATING TEMPERATURE	-30°C to +85°C (-22°F to +185°F)	RATED OPERATIONAL VOLTAGE	10-30 VDC	MAX. RIPPLE	≤10%
SPECIFICATIONS																				
RATED OPERATING DISTANCE	4mm =.158"																			
MOUNTING MODE	FLUSH																			
MIN. REPEAT ACCURACY	≤ 2%																			
TEMPERATURE DRIFT	≤±10% ≤±15%, ≤ -25°C v ≥ +70°C																			
HYSTERESIS (SWITCHING DISTANCE)	3-15%																			
OPERATING TEMPERATURE	-30°C to +85°C (-22°F to +185°F)																			
RATED OPERATIONAL VOLTAGE	10-30 VDC																			
MAX. RIPPLE	≤10%																			
SHORT-CIRCUIT AND OVERLOAD PROTECTED																				

A	DRAWING RELEASE	RDS	05/18/06	
REV	DESCRIPTION	BY	DATE	ECO NO.

RELATED DOCUMENTS 1. 2. 3. 4.		3RD ANGLE PROJECTION 		THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
MATERIAL		DRFT RDS DSGN TB		DATE 05/18/06 SCALE 1=1.0		DESCRIPTION BI 4U-EM12-AN6X-H1141	
FINISH		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT INCH [MILLIMETER]		IDENTIFICATION NO. M1634827	
		DO NOT SCALE THIS DRAWING		FILE: M1634827		REV A	
						SHEET 1 OF 1	

SOURCE DRAWING - FOR REFERENCE ONLY