


1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

DO NOT SCALE		DIMENSIONS IN MM.		
PART NUMBER	MATERIAL	FINISH	REELING	LOOSE PIECE (REF. ONLY)
154717-1	BRASS	NONE	STANDARD	341001-1
154717-2	PHOS. BRONZE	NONE	STANDARD	341001-2
154717-3	BRASS	TIN	STANDARD	341001-3
154717-4	PHOS. BRONZE	TIN	STANDARD	341001-4
154717-5	PHOS. BRONZE	NONE	STANDARD	341001-5
154717-6	BRASS	PRE-TIN	STANDARD	341001-6
154717-7	PHOS. BRONZE	PRE-TIN	STANDARD	341001-7
154717-8	PHOS. BRONZE	SILVER	STANDARD	341001-8
154717-9	BRASS	SILVER	STANDARD	341001-9
1-154717-0	OBSOLETE	OBSOLETE	OBSOLETE	---
1-154717-1	BRASS	NONE	REV. REEL VERSION-1	---
1-154717-2	PHOS. BRONZE	NONE	REV. REEL VERSION-2	---
1-154717-3	PHOS. BRONZE	PRE-TIN	STANDARD	---
1-154717-4	BRASS	TIN	REV. REEL VERSION-3	---
1-154717-5	PHOS. BRONZE	TIN	REV. REEL VERSION-4	---
1-154717-6	PHOS. BRONZE	TIN	STANDARD (SPLICE FREE VERSION)	---



WIRE RANGE 2.5 TO 4.0mm²

INSULATION RANGE 3.6 TO 4.3mm DIA.

CUSTOMER DWG
FOR REFERENCE ONLY

RELEASED FOR PUBLICATION
ORIGINAL 1974

- - - -

TOLERANCES
UNLESS OTHERWISE
STATED
DEC ± 0.5
ANGLES ± 1°

DR. D.A.BARRATT

27.11.91

CH. D.TERRY

APP. D.A.BARRATT



TE Connectivity

NAME

POSITIVE LOCK RECEPTACLE

AR2 REVISED PER ECO-11.005150 RK/HMR 28MAR11

SCALE

LOC

SIZE

DWG.No.

REV

SHEET

REV ECN APPROVED DATE

4/1

E

A4

C154717

AR2

1/1