

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F





E

D

C

B

A



注記 NOTES :
1. 一般公差 : ±0.4
GENERAL TOLERANCES: ±0.4

OVERALL TIN 0.88μmin	39000342	2478TL	LOOSE
OVERALL COPPER 0.54μmin	39000286	2478T	CHAIN
ニッケル下地 2 μmMIN.	39-00-0344	2478GL	バラ状 LOOSE
金 0.35 μmMIN.	39-00-0343	2478G	チェーン状 CHAIN
GOLD 0.35 μmMIN. OVER			
NICKEL 2 μmMIN.			
メッキ PLATING	EDP NO.	ENG.NO.	形状 FORM

MATERIAL
BRASS t = 0.254

ENTER DESCRIPTION	EC NO: I2010-0695	2010/06/23	2010/07/28
DRWN: NS01	CHKD: HIRAMOT	1996/01/30	APPR: KPRASAD
REV	DESCRIPTION	DATE	DATE

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± 0.2	± ---
3 PLACES	± 0.25	± ---
2 PLACES	± 0.3	± ---
1 PLACE	± 0.01	± ---
ANGULAR ± 3 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	
MM ONLY	
DRAWN BY	DATE
HHASEGAW	1993/04/23
CHECKED BY	DATE
HHIRAMOT	1996/01/30
APPROVED BY	DATE
MFUKUSHI	1996/01/30
MATERIAL NO.	
SEE CHART	
SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
A3	

MOLEX INCORPORATED	SHEET NO.
SD-2478*	1 OF 1

9 8 7 6 5 4 3 2 1