

Vital 117

Chemical Product	CAS #	BTT (minutes)	Permeation level	Standard	Degradatio level	Rating
2-Butoxyethanol (Butyl Cellusolve) 99%	111-76-2	21	1	ASTM F739	4	+
2-Ethoxyethanol (Cellosolve) 99%	110-80-5	27	1	ASTM F739	4	+
2-Ethoxyethyl acetate (Cellosolve Acetate) 99%	111-15-9	15	1	ASTM F739	3	=
2-Propanol (Isopropanol) 99%	67-63-0	15	1	EN 374-3:2003	4	+
Acetaldehyde 99%	75-07-0	5	0	ASTM F739	4	=
Acetic acid 10%	64-19-7	NT	NT		4	NA
Acetic acid 50%	64-19-7	254	5	ASTM F739	4	++
Acetic acid 99%	64-19-7	8	0	EN 374-3:2003	4	=
Acetone 99%	67-64-1	7	0	ASTM F739	3	=
Ammonium hydroxide solution 29%	1336-21-6	16	1	ASTM F739	4	+
Aniline 99%	62-53-3	67	3	ASTM F739	4	++
Dimethylformamide 99%	68-12-2	12	1	EN 374-3:2003	4	+
Dimethylsulfoxide 99%	67-68-5	216	4	ASTM F739	4	++
Ethanol 95%	64-17-5	14	1	EN 374-3:2003	4	+
Ethylene glycol 99%	107-21-1	480	6	ASTM F739	4	++
Formaldehyde 30%	50-00-0	NT	NT		4	NA
Formaldehyde 37%	50-00-0	480	6	ASTM F739	4	++
Glutaraldehyde 50%	111-30-8	NT	NT		4	NA
Hydrazine 35%	302-01-2	NT	NT		4	NA
Hydrazine 70%	302-01-2	115	3	ASTM F739	4	++
Hydrazine 98%	302-01-2	NT	NT		4	NA
Hydrochloric acid 10%	7647-01-0	480	6	EN 374-3:2003	4	++
Hydrochloric acid 35%	7647-01-0	480	6	EN 374-3:2003	4	++
Hydrochloric acid 37%	7647-01-0	43	2	ASTM F739	4	+
m-Cresol 97%	108-39-4	145	4	ASTM F739	4	++
Methanol 85%	67-56-1	NT	NT		4	NA

*not normalized result

Overall Chemical Protection Rating

Protection rating is determined by taking into account the effects of both permeation and degradation in an attempt to provide users with an overall protection guideline when using our glove products against specific chemicals.

- Used for **high chemical exposure** or chemical immersion, limited to BTT based on a working day.
- Used for **repeated chemical contact**, limited to total chemical exposure i.e. : accumulative BTT based on a working day.
- **Splash protection only**, on chemical exposure the gloves should be discarded and new gloves worn as soon as possible.
- **Not recommended**, these gloves are deemed unsuitable for work with this chemical.
- NT : Not tested
- NA : Not applicable because not fully tested (only degradation OR permeation results)

The chemical test data and overall chemical protection rating should not be used as the absolute basis for glove selection. Actual in-use conditions may vary glove performance from the controlled conditions of laboratory tests. Factors other than chemical contact time, such as concentration and temperature, glove thickness and glove reuse, may also affect performance. Other glove requirements, such as length, dexterity, cut, abrasion, puncture and snag resistance, or glove grip also need to be considered in making your final selection.

Vital 117

Chemical Product	CAS #	BTT (minutes)	Permeation level	Standard	Degradatio level	Rating
Methanol 99%	67-56-1	7	0	EN 374-3:2003	4	=
Methyl Ethyl Ketone (2-Butanone) 99%	78-93-3	2	0	EN 374-3:2003	2	-
N-methyl-2-Pyrrolidone 99%	872-50-4	17	1	EN 374-3:2003	4	+
N-N dimethyl acetamide 30%	127-19-5	NT	NT		4	NA
N-N dimethyl acetamide 99%	127-19-5	39	2	ASTM F739	4	+
Nitric acid 10%	7697-37-2	480	6	ASTM F739	4	++
Nitric acid 20%	7697-37-2	480	6	ASTM F739	4	++
Nitric acid 40%	7697-37-2	480	6	ASTM F739	4	++
Nitric acid 50%	7697-37-2	480	6	ASTM F739	4	++
Phenol 85%	108-95-2	77	3	ASTM F739	4	++
Phosphoric acid 75%	7664-38-2	480	6	ASTM F739	4	++
Phosphoric acid 85%	7664-38-2	480	6	ASTM F739	4	++
Potassium Hydroxide 50%	1310-58-3	480	6	ASTM F739	4	++
Skydrol LD-4 mixture	NA	60	2	ASTM F739	NT	NA
Sodium hydroxide 20%	1310-73-2	480	6	EN 374-3:2003	4	++
Sodium hydroxide 40%	1310-73-2	480	6	ASTM F739	4	++
Sodium hydroxide 50%	1310-73-2	480	6	ASTM F739	4	++
Sulfuric acid 10%	7664-93-9	480	6	ASTM F739	4	++
Sulfuric acid 40%	7664-93-9	480	6	ASTM F739	4	++
Sulfuric acid 50%	7664-93-9	480	6	ASTM F739	4	++
Toluene Diisocyanate (TDI) 80%	584-84-9	480	6	ASTM F739	3	++
Triethanolamine 98%	102-71-6	480	6	ASTM F739	4	++

*not normalized result

Overall Chemical Protection Rating

Protection rating is determined by taking into account the effects of both permeation and degradation in an attempt to provide users with an overall protection guideline when using our glove products against specific chemicals.

- Used for **high chemical exposure** or chemical immersion, limited to BTT based on a working day.
- Used for **repeated chemical contact**, limited to total chemical exposure i.e. : accumulative BTT based on a working day.
- **Splash protection only**, on chemical exposure the gloves should be discarded and new gloves worn as soon as possible.
- **Not recommended**, these gloves are deemed unsuitable for work with this chemical.

 NT : Not tested

 NA : Not applicable because not fully tested (only degradation OR permeation results)

The chemical test data and overall chemical protection rating should not be used as the absolute basis for glove selection. Actual in-use conditions may vary glove performance from the controlled conditions of laboratory tests. Factors other than chemical contact time, such as concentration and temperature, glove thickness and glove reuse, may also affect performance. Other glove requirements, such as length, dexterity, cut, abrasion, puncture and snag resistance, or glove grip also need to be considered in making your final selection.