

## PARATHOM MR16 35 36° ADV 6.5 W/840 GU5.3

PARATHOM MR16 advanced | Dimmable low-voltage LED reflector lamps MR16 with retrofit pin base



### Areas of application

- As a downlight for marking walkways, doors, stairs, etc.
- Exhibitions, department stores
- Outdoor use in outdoor luminaires only (minimum IP65)
- Directional light sources
- Museums
- Hospitality
- Shops

### Product benefits

- Very low energy consumption
- Extremely long life
- Robust against vibrations
- No UV and near-IR radiation in the light beam
- Efficient generation of white light

### Product features

- Professional LED lamp
- Dimmable (with many common dimmers, see also [www.osram.com/dim](http://www.osram.com/dim))
- Base: GU5.3
- Lifetime: up to 25,000 h
- Mercury-free lamps
- High color consistency



## Technical data

### Electrical data

Rated wattage	5.90 W
Nominal wattage	5.90 W
Nominal voltage	12 V
Claimed equiv. conventional lamp power	35 W
Operating frequency	50...60 Hz
Power factor $\lambda$	0.70

### Photometrical data


Luminous intensity	830 cd
Nominal luminous flux	350 lm
Rated luminous flux	350 lm
Color temperature	4000 K
Color rendering index Ra	80
Lumen main.fact.at end of nom.life time	0.70
Light color as per EN 12464-1	Cool White
Standard deviation of color matching	$\leq 5$ sdcn
Nominal useful luminous flux 90°	365 lm
Rated useful luminous flux 90°	365 lm
Rated peak intensity	780 cd

### Light technical data

Beam angle	36 °
Warm-up time (60 %)	0.20 s
Starting time	0.1 s
Nominal beam angle	36.00 °
Rated beam angle (half peak value)	36.00 °

### Dimensions & weight

## Product datasheet



<b>Overall length</b>	51.0 mm
<b>Diameter</b>	50.0 mm
<b>Outer bulb</b>	MR51
<b>Length</b>	51.0 mm
<b>Maximum diameter</b>	50.0 mm

### Lifespan

<b>Nominal lamp life time</b>	25000 h
<b>Rated lamp life time</b>	25000 h
<b>Number of switching cycles</b>	100000

### Additional product data

<b>Base (standard designation)</b>	GU5.3
<b>Lamp mercury content</b>	0.0 mg
<b>Mercury-free</b>	Yes
<b>New article</b>	NEW
<b>Appropriate disposal acc. to WEEE</b>	Yes
<b>Footnote only for product</b>	All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value/LED lamps contain several electronic components. Under unfavourable conditions these can lead to acoustic noise. In case of resonance even low noise can cause audible effect. Possible factors influencing this are the installation, the design of the lamp holder and the luminaire (acoustic resonance effect) as well as the dimmer or the transformer (harmonics or electronic resonance)

### Capabilities

<b>Dimmable</b>	Yes <sup>1)</sup>
-----------------	-------------------

# Product datasheet

<sup>1)</sup> With many common dimmers

## Certificates & standards


Energy efficiency class	A
Energy consumption	7 kWh/1000h

## Country specific categorizations

ILCOS	DRPAR-6,5/840-12-GU5.3-50/36
Order reference	PMR163536AD 5.9

## Light Distribution

---



---

Spectral power distribution

## Product datasheet



---

Guarantee

---

### Equipment / Accessories

- Equipped with high-power LEDs
- Suitable for many commercially available electronic or conventional transformers

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4008321885203	PARATHOM MR16 35 36° ADV 6.5 W/840 GU5.3	Shipping carton box 10	71 mm x 114 mm x 271 mm	2.19 dm <sup>3</sup>	617.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### References / Links

For dimming conformity see

- ▶ [www.osram.com/DIM](http://www.osram.com/DIM)

For further products and actual information concerning LED lamps see

- ▶ [www.osram.com/ledlamps](http://www.osram.com/ledlamps)

For Guarantee see

- ▶ [www.osram.com/guarantee](http://www.osram.com/guarantee)

Further information see

- ▶ [www.osram.com/low-voltage-ledlamps](http://www.osram.com/low-voltage-ledlamps)

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.