

Enamelled copper wire on mini bobbin
CUL 500/0,85



Advantages

Insulating varnish basis min. polyurethane, mod. current loading

Degree 1

TJ min. 155 °C

Solderable

Applications

Enamelled copper wire for the production of coils and winding and for general laboratory needs.

Approvals



Enamelled copper wire on mini bobbin **CUL 500/0,85**

Type	CUL 500/0,85	Type	CUL 500/0,85	
Electrical data	30		Operating data	
			current car. cap.	2.00 A
			Environment	
			Heat resistance	155 °C (CL.F)
			insulating varnish	min. Polyurethan, mod.
			Tin-plate	>350 °C
			Measures and weights	
			Wire diameter	0.85 mm
			Weight	0.50 kg
			Length m (min.)	77

Subjects to change.