

D





FIG. 2

C






FIG. 1

B



RECOMMENDED MOUNTING HOLE PATTERN FOR .063 THICK P.C. BOARD (feature 2)

A

METRIC			
.073	1.85		
.070	1.78		
.068	1.73		
.065	1.65	1.000	25.40
.063	1.60	.450	11.43
.060	1.52	.425	10.80
.045	1.14	.400	10.16
.030	0.76	.345	8.76
.015	0.38	.325	8.26
.012	0.30	.300	7.62
.010	0.25	.212	5.38
.008	0.20	.180	4.57
.005	0.13	.156	3.96
.003	0.08	.125	3.18
.001	0.03	.078	1.98
IN	MM	IN	MM
CONVERSION TABLE			

- 1 POST TO WITHSTAND 13 NEWTONS (3LBS.) MIN. AXIAL FORCE IN BOTH DIRECTIONS SHOWN WITHOUT DISLODGING.
- 2 TOLERANCES APPLY TO SOLDER SIDE OF BOARD.
- 3 MEASURED AT SURFACE (A)
- 4 PLASTIC FLASH PERMITTED IN THIS AREA.
- 5 PARTS COMPLY WITH AMP SOLDERABILITY SPEC. NO. 109-11-2.
- 6 ONE HOLE MAY BE UNDERSIZED (.065/.060 DIA.) FOR ASSEMBLY RETENTION DURING WAVE SOLDERING.
- 7 MATERIAL: HEADER-THERMOPLASTIC POLYESTER GLASS-FILLED 94V-O(NATURAL)(FIG.2) POST-COPPER ALLOY (TIN PLATED)
- MATERIAL: HEADER-THERMOPLASTIC POLYESTER NON-FILLED 94V-O(NATURAL)(FIG.1) POST-COPPER ALLOY (TIN PLATED)
- 8 COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
- 9 PLASTIC BURRS CAUSED BY CUT-OFF TOOLING ARE PERMITTED WITHIN THE MAXIMUM TOLERANCE ENVELOPE.
- 10 POST TO BE MEASURED WHEN STRIP IS HELD FLAT.
- 11 POST MUST WITHSTAND TWO 90° BENDS AGAINST EXTRUSION WITHOUT BREAKING.
- 12 DIMENSION SHOULD BE .325-.400 WHEN MATING WITH A MTA 156 CONNECTOR ASSEMBLY OR .325-.345 WHEN MATING WITH A SL-156 CONNECTOR ASSEMBLY.
- 13 PIN BURR OF .005 MAX. VERTICAL AND .003 MAX. HORIZONTAL PERMITTED AT POST TIPS ON BOTH ENDS.

2	95.10	3.744	24	2-640389-4
1	91.14	3.588	23	2-640389-3
1	87.17	3.432	22	2-640389-2
1	83.21	3.276	21	2-640389-1
1	79.25	3.120	20	2-640389-0
1	75.29	2.964	19	1-640389-9
1	71.32	2.808	18	1-640389-8
1	67.36	2.652	17	1-640389-7
1	63.40	2.496	16	1-640389-6
1	59.44	2.340	15	1-640389-5
1	55.47	2.184	14	1-640389-4
1	51.51	2.028	13	1-640389-3
1	47.55	1.872	12	1-640389-2
1	43.59	1.716	11	1-640389-1
1	39.62	1.560	10	1-640389-0
2	35.66	1.404	9	640389-9
1	31.70	1.248	8	640389-8
1	27.74	1.092	7	640389-7
1	23.77	.936	6	640389-6
1	19.81	.780	5	640389-5
1	15.85	.624	4	640389-4
1	11.89	.468	3	640389-3
1	7.92	.312	2	640389-2
FIG NO	MM	IN	NUMBER OF POSITIONS	PART NUMBER
	L			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S. HOOVER 05-NOV-2002
CHK D. BOSSI 05-NOV-2002
APVD D. BOSSI 05-NOV-2002

NAME Tyco Electronics Corporation
Harrisburg, PA 17105-3608

DIMENSIONS: MM [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ± .005
4 PLC ±
ANGLES ± °
FINISH

PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

SIZE CAGE CODE DRAWING NO
A1 00779 ©=640389

RESTRICTED TO

SCALE 5:1 SHEET 1 OF 1 REV Y