


APPLICATION

Triple protected highly flexible PVC insulated and sheathed power cable for exceptional mechanical and electrical protection, generally in accordance with VDE0250

CONSTRUCTION



1. Conductor	Material Dimensions	Stranded bare copper 32x0.20 mm (1.00 mm ²)
2. Insulation	Material Diameter	PVC 2.52 ± 0.05 mm
3. Stranding	Lay up Colours	3 + 6 cores stranded black numbered and yellow/green
4. Foil	Material Thickness	Polyester foil 23 µm
5. Bedding	Material Diameter Nominal wall	PVC 11.40 ± 0.20 mm 0.45 mm
6. Armour	Material Diameter Coverage	Galvanized steel wire 12.48 mm 64 %
7. Jacket	Material Diameter Nominal wall	PVC 14.68 ± 0.30 mm 1.10 mm

CONTROLFLEX SY LEADFREE
12*1.00 mm2 blk.**REQUIREMENTS AND TEST METHODS****Electrical:**

Voltage rating conductor to earth	300 V RMS
Voltage rating conductor to conductor	500 V RMS
Maximum resistance conductor @ 20°C	19.5 Ω/km
Maximum continuous current per conductor @ 25°C	0.7 x 10 A

Mechanical and physical:

Temperature range processing	-5 to +70 °C
Temperature range operating (moving installation)	-5 to +70 °C
Temperature range operating (fixed installation)	-30 to +70 °C
Temperature range storage	-30 to +70 °C
Nominal weight per 100m	34.2 kg
Maximum pulling tension	840 N
Minimum bending radius	10 x D



Belden CDT believes this product to be in compliance with the environmental regulations EU RoHS (Directive 2002/95/EC, 27 January 2003); this is valid for all material produced after the RoHS compliant date for this product.