

19.5" HD+ LED Monitor

Art. no. TVAC10031

Page 1 of 2



- Resolution: 1600 x 900 pixels
- Fast reaction time (5 ms)
- LED background lighting: brilliant colour display and contrast
- Graphical on-screen display (OSD)
- Connections: HDMI, DVI, VGA, audio input and output
- Integrated loudspeakers
- Low power consumption (LED technology)
- For wall and ceiling installation (with VESA mount)

The 19.5" HD+ LED monitor offers sharp images in 16:9 format and is ideal for surveillance projects with an ABUS recorder. High-resolution images are displayed via an HDMI cable.

Detailed surveillance pictures

Thanks to its high resolution, outstanding picture fidelity and rapid reaction time, the monitor produces accurate surveillance pictures. The LED backlighting ensures optimum contrast and an extremely realistic colour display.

Versatile connections

The HDMI, VGA and DVI video inputs offer flexibility for connecting the monitor to a recorder or a computer. Integrated loudspeakers and audio inputs also allow sound signals to be played back. All of these features make the monitor a cost-effective component for versatile surveillance and IT systems.

Energy efficiency

The energy-efficient LED display ensures very low power consumption.

Easy installation

VESA standard mounts allow mounting to a wall or ceiling. This makes installation fast and easy.

19.5" HD+ LED Monitor

Art. no. TVAC10031

Page 2 of 2

Technical Data:

Dimensions	(WxHxD) 470x360x143 mm
Connection type	1x VGA,1xDVI,1xHDMI, 1x Audio
Horizontal/vertical viewing angle	75/80 °
Picture format	16:9
Screen diagonal	19.5 "
Width	470 mm
Display surface	matte
Color levels	16.2 MIO
Frequency range	40-80KHz (H) / 55-75Hz (V) GHz
Housing material	Plastic
Brightness	250 cd/m ²
Height	360 mm
Comb filter	3D

Contrast ratio	1000:1
Loudspeaker	2
Max. humidity	70 %
Monitor type	Standard TFT
Net weight	2.8 kg
Pixel pitch	0,294 x0,294 (H) x (V) mm
Reaction time	5 ms
Signal detection	Automatic
DC voltage supply	12 V
OSD language	multilingual
Power consumption	2500 mA