

Interface module - VIP-3/PT/D37SUB/M/HW/C300 - 2904276

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE module, with push-in connections and male D-SUB miniature pin strip, for mounting on NS 35 rails, 37-pos.


The figure shows a version with a screw connection

Why buy this product

- These VARIOFACE modules are used in combination with the relevant front adapters



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 812610
Weight per Piece (excluding packing)	221.0 g
Custom tariff number	85369010
Country of origin	United States
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	87.6 mm
Height	75.8 mm
Depth	63 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	125 V AC/DC
Max. perm. current (per branch)	2 A
Number of positions	37

Interface module - VIP-3/PT/D37SUB/M/HW/C300 - 2904276

Technical data

General

Status display	No
Mounting position	any
Standards/regulations	EN 50178
Rated surge voltage	1.2 kV
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Push-in connection
Number of positions	37
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Stripping length	8 mm

Connection data for connection 2

Connection name	D-SUB connection
Number of connections	1
Connection method	D-SUB pin strip
Number of positions	37

Supported controller

Controller	HONEYWELL C300
- suitable I/O card	TAIX01 (non-redundant)
	TAIX11 (redundant)

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

Interface module - VIP-3/PT/D37SUB/M/HW/C300 - 2904276

Classifications

ETIM

ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

CSA	
mm ² /AWG/kcmil	26-14
Nominal current I _N	2 A
Nominal voltage U _N	105 V

UL Recognized	
mm ² /AWG/kcmil	26-14
Nominal current I _N	2 A
Nominal voltage U _N	125 V

Interface module - VIP-3/PT/D37SUB/M/HW/C300 - 2904276

Approvals


cUL Recognized	
mm ² /AWG/kcmil	26-14
Nominal current I _N	2 A
Nominal voltage U _N	125 V

EAC

cULus Recognized

Drawings

Circuit diagram



Connection scheme VIP-3/SC/D37SUB/M/HW/C300