

High Power SPT⁺ & Rugged Type IGBT Module

Description

DAWIN'S IGBT 7DM-3 Package devices are optimized to reduce losses and switching noise in high frequency power conditioning electrical systems. These IGBT modules are ideally suited for power inverters, motors drives and other applications where switching losses are significant portion of the total losses.


Features

- ☞ High Speed Switching
- ☞ $BV_{CES} = 1200V$
- ☞ Low Conduction Loss : $V_{CE(sat)} = 1.9V$ (typ.)
- ☞ Fast & Soft Anti-Parallel FWD
- ☞ Short circuit rated : Min. 10uS at $T_c = 100^\circ C$
- ☞ Reduced EMI and RFI
- ☞ Isolation Type Package

Applications

Motor Drives, High Power Inverters, Welding Machine, Induction Heating, UPS, CVCF, Robotics, Servo Controls, High Speed SMPS

Equivalent Circuit and Package



Please see the package out line information

Absolute Maximum Ratings @ $T_J = 25^\circ C$ (Per Leg)

Symbol	Parameter	Conditions	Ratings	Unit
V_{CES}	Collector-Emitter Voltage	-	1200	V
V_{GES}	Gate-Emitter Voltage	-	± 20	V
I_C	Collector Current	$T_c = 25^\circ C$	275	A
		$T_c = 80^\circ C$	200	A
$I_{CM(1)}$	Pulsed Collector Current	-	400	A
I_F	Diode Continuous Forward Current	$T_c = 100^\circ C$	200	A
I_{FM}	Diode Maximum Forward Current	-	400	A
T_{SC}	Short Circuit Withstand Time	$T_c = 100^\circ C$	10	uS
P_D	Maximum Power Dissipation	$T_c = 25^\circ C$	1350	W
T_J	Operating Junction Temperature	-	-40 ~ 150	$^\circ C$
T_{stg}	Storage Temperature Range	-	-40 ~ 125	$^\circ C$
V_{iso}	Isolation Voltage	AC 1 minute	2500	V
TL	Maximum Lead Temp. for soldering Purposes, 1/8" from case for 9 seconds	-	260	$^\circ C$
	Mounting screw Torque :M6	-	4.0	N.m
	Power terminals screw Torque :M6	-	4.0	N.m

Note : (1) Repetitive rating : Pulse width limited by max. junction temperature

Electrical Characteristics of IGBT @ $T_C=25^\circ\text{C}$ (unless otherwise specified)

Symbol	Parameter	Conditions	Values			Unit
			Min.	Typ.	Max.	
BV_{CES}	C - E Breakdown Voltage	$V_{GE} = 0V, I_C = 1.0mA$	1200	-	-	V
$\Delta BV_{CES}/\Delta T_J$	Temperature Coeff. of Breakdown Voltage	$V_{GE} = 0V, I_C = 1.0mA$	-	0.6	-	V/°C
$V_{GE(th)}$	G - E threshold voltage	$I_C = 5.0mA, V_{CE} = V_{GE}$	5	-	8	V
I_{CES}	Collector cutoff Current	$V_{CE} = 1200V, V_{GE} = 0V$	-	-	2.0	mA
I_{GES}	G - E leakage Current	$V_{GE} = \pm 20V$	-	-	± 300	nA
$V_{CE(sat)}$	Collector to Emitter saturation voltage	$I_C = 200A, V_{GE} = 15V @ T_C = 25^\circ\text{C}$	-	1.9	2.6	V
		$I_C = 200A, V_{GE} = 15V @ T_C = 100^\circ\text{C}$	-	2.2	-	V
C_{ies}	Input capacitance	$V_{GE} = 0V, f = 1MHz$	-	15	-	nF
C_{oes}	Output capacitance	$V_{CE} = 25V$	-	1.1	-	nF
C_{res}	Reverse transfer capacitance		-	0.7	-	nF
$t_{d(on)}$	Turn on delay time	$V_{CC} = 600V, I_C = 200A$	-	190	-	nS
t_r	Turn on rise time	$V_{GE} = \pm 15V$	-	100	-	nS
$t_{d(off)}$	Turn off delay time	$R_G = 5.1\Omega$	-	500	-	nS
t_f	Turn off fall time	Inductive Load, @ $T_C=25^\circ\text{C}$	-	100	-	nS
E_{on}	Turn on Switching Loss		-	13	-	mJ
E_{off}	Turn off Switching Loss		-	9	-	mJ
E_{ts}	Total Switching Loss		-	22	-	mJ
T_{sc}	Short Circuit Withstand Time	$V_{CC} = 600V, V_{GE} = \pm 15V$ @ $T_C = 100^\circ\text{C}$	10	-	-	uS
Q_g	Total Gate Charge	$V_{CC} = 600V$	-	1400	-	nC
Q_{ge}	Gate-Emitter Charge	$V_{GE} = \pm 15V$	-	250	-	nC
Q_{gc}	Gate-Collector Charge	$I_C = 200A$	-	800	-	nC

Electrical Characteristics of FRD @ T_c=25°C (unless otherwise specified)

Symbol	Parameter	Conditions	Values			Unit
			Min.	Typ.	Max.	
V _{FM}	Diode Forward Voltage	I _F =200A T _c =25°C	-	1.9	2.1	V
			T _c =100°C	-	2.0	
t _{rr}	Diode Reverse Recovery Time	I _F =200A, V _R =600V di/dt=-400A/uS	T _c =25°C	-	180	nS
			T _c =100°C	-	200	
I _{rr}	Diode Peak Reverse Recovery Current		T _c =25°C	-	75	A
			T _c =100°C	-	90	
Q _{rr}	Diode Reverse Recovery Charge		T _c =25°C	-	6750	nC
			T _c =100°C	-	9000	

Thermal Characteristics and Weight

Symbol	Parameter	Conditions	Values			Unit
			Min.	Typ.	Max.	
R _{θJC}	Junction-to-Case(IGBT Part, Per 1/2 Module)		-	-	0.09	°C/W
R _{θJC}	Junction-to-Case(DIODE Part, Per 1/2 Module)		-	-	0.22	°C/W
R _{θCS}	Case-to-Sink (Conductive grease applied)		0.025	-	-	°C/W
Weight	Weight of Module		-	-	360	g

Performance Curves




Fig 1. Typical Output characteristics




Fig 2. Typical Output characteristics




Fig 3. Typical Saturation Voltage characteristics




Fig 4. Load Current vs. Frequency




Fig 5. Typical Saturation Voltage vs. V_{GE}




Fig 6. Typical Saturation Voltage vs. V_{GE}




Fig 7. Capacitance characteristics




Fig 8. Gate Charge characteristics




Fig 9. rated Current vs. Case Temperature




Fig 10. Power Dissipation vs. Case Temperature




Fig 11. Transient Thermal Impedance




Fig 12. Forward characteristics

7DM-3

