

We measure it.



Infrared temperature measuring instrument

testo 830

Fast and universal non-contact measurement of surface temperature

Laser measurement point marker and large optics for exact measurement even at greater distances

Fast recording of measurement values (two measurements per second)

Settable emissivity

Two adjustable alarm limit values

Good handling thanks to ergonomic "pistol design"



The testo 830 is a fast, universally applicable infrared thermometer for non-contact measurement of surface temperatures. The instrument has a handy pistol design and is available in four versions:

The infrared measurement of the **testo 830-T1** takes place with a 1-point laser measurement point marker and 10:1 optics.

The **testo 830-T2** has a 2-point laser measurement point marker and 12:1 optics.

The **testo 830-T3** is specially suited to temperature measurements on surfaces with a small diameter. A two-point laser marks the measurement point exactly.

Thanks to the 2-point laser marker and 30:1 optics, the **testo 830-T4** can measure the surface temperature of small objects at a safe distance. The measurement point diameter is only 36 mm at a distance of 1 m. The possibility of connecting external probes also exists.

www.testo.com

Infrared temperature measuring instruments

testo 830

Infrared thermometer with 1-point laser sighting

testo 830-T1

testo 830-T1, infrared thermometer, 1 point laser sighting, 10:1 optics, adjustable limit values, alarm function, incl. Batteries and factory calibration certificate

Part no. 0560 8301



Infrared thermometer with 2-point laser sighting and connection for external probes

testo 830-T2

testo 830-T2, infrared thermometer, 2-point laser sighting, 12:1 optics, adjustable limit values, alarm function, connection of external probes, incl. Batteries and factory calibration certificate

Part no. 0560 8302



The fast and universal infrared thermometer with 1-point laser sighting and 10:1 optics in ergonomic "pistol design"

- Fast readings
- Laser sighting
- Adjustable alarm limits
- Audible and visual alarm if limits are exceeded
- User-friendly thanks to "Pistol design"
- Backlit display
- Adjustable emission factor (0.2 to 1.0)

testo 830-T2 Set

Set testo 830-T2, infrared thermometer with protective leather case, incl. cross-band surface probe, Batteries and factory calibration certificate

Part no. 0563 8302

The fast and versatile infrared thermometer with 2-point laser marking and 12:1 optics. Possibility of connecting an external Type K probe for contact measurement.

In addition to the benefits of testo 830-T1:

- 2-point laser sighting
- Contact measurement with connectable temperature probe
- Emissivity determination with external TC probe

Infrared temperature measuring instruments

testo 830

Infrared thermometer with close focus optics for measuring small objects

testo 830-T3

testo 830-T3, infrared thermometer with close focus optics, 2-point laser sighting, adjustable limit values, alarm function, contact temperature probe attachable, incl. Batteries and factory calibration certificate

Part no. 0560 8303



The fast infrared thermometer testo 830-T3 is especially suited to temperature measurements on surfaces with a small diameter. A two-point laser marks the measurement point exactly.

- Small measurement point of 2 mm, distance 25 mm
- °C contact measurement with attachable TC probe
- Backlit display
- Audible and optical alarm when limit values are exceeded
- Emissivity adjustable 0.2 to 1.0

Infrared thermometer with 30:1 optics for exact measurement at a distance

testo 830-T4

testo 830-T4, infrared thermometer, 2-point laser sighting, 30:1 optic, adjustable limit values, alarm function, connection of external probes, incl. Batteries and factory calibration certificate

Part no. 0560 8304



Set testo 830-T4

Set testo 830-T4, infrared thermometer with protective leather case, incl. cross-band surface probe, battery and factory calibration certificate

Part no. 0563 8304

The fast and versatile infrared thermometer with 2-point laser marking and 30:1 optics. The surface temperature, also of smaller objects, can be measured at a safe distance. The diameter of the measurement spot is only 36 mm at a distance of 1 m. Possibility of connecting external temperature probes.

- 30:1 optics for measuring temperature at a distance, even on small objects
- °C contact measurement with connectable TC probe
- Emissivity determination with external temperature probe
- Input of upper and lower limit value
- Audible and optical alarm when limit values are exceeded
- Display illumination

Technical data

Common technical data for all versions

Spectral range	8 to 14 μm
Emissivity	Adjustable 0.2 to 1.0
Storage temp.	-40 to +70 $^{\circ}\text{C}$
Oper. temp.	-20 to +50 $^{\circ}\text{C}$

Battery type	9V block battery
Battery life	15 h
Weight	200 g
Dimensions	190 x 75 x 38 mm
Material/Housing	ABS


Varying technical data

	testo 830-T1	testo 830-T2	testo 830-T3	testo 830-T4
Meas. range				
Infrared	-30 to +400 $^{\circ}\text{C}$	-30 to +400 $^{\circ}\text{C}$	-25 to +400 $^{\circ}\text{C}$	-30 to +400 $^{\circ}\text{C}$
Type K (NiCr-Ni)	–	-50 to +500 $^{\circ}\text{C}$	-50 to +500 $^{\circ}\text{C}$	-50 to +500 $^{\circ}\text{C}$
Accuracy ± 1 digit				
Infrared	$\pm 1.5^{\circ}\text{C}$ or 1.5 % of mv (+0.1 to +400 $^{\circ}\text{C}$) $\pm 2^{\circ}\text{C}$ or $\pm 2\%$ of mv (-30 to 0 $^{\circ}\text{C}$) the higher value applies	$\pm 1.5^{\circ}\text{C}$ or $\pm 1.5\%$ of mv (+0.1 to +400 $^{\circ}\text{C}$) $\pm 2^{\circ}\text{C}$ or $\pm 2\%$ of mv (-30 to 0 $^{\circ}\text{C}$) the higher value applies	$\pm 1^{\circ}\text{C}$ (-20 to +100 $^{\circ}\text{C}$) $\pm 2^{\circ}\text{C}$ or $\pm 2\%$ of mv (remaining range)	$\pm 1.5^{\circ}\text{C}$ (-20 to 0 $^{\circ}\text{C}$) $\pm 2^{\circ}\text{C}$ (-30 to -20,1 $^{\circ}\text{C}$) $\pm 1^{\circ}\text{C}$ or 1% of mv (remaining range)
Type K (NiCr-Ni)	–	$\pm 0.5^{\circ}\text{C}$ +0.5% of mv	$\pm 0.5^{\circ}\text{C}$ +0.5% of mv	$\pm 0.5^{\circ}\text{C}$ +0.5% of mv
Resolution	0.5 $^{\circ}\text{C}$	0.5 $^{\circ}\text{C}$	0.5 $^{\circ}\text{C}$	0.1 $^{\circ}\text{C}$
Measurement rate				
Infrared	0.5 s	0.5 s	0.5 s	0,5 s
Type K (NiCr-Ni)	–	1.75 s	1.75 s	1.75 s
Meas. spot marking	1-point laser	2-point laser	2-point laser	2-point laser
Distance to measurement spot	10:1	12:1	2.5:1 2 mm @ 25 mm (90%)	30:1 (typical at a distance of 0.7 m to the measurement object 24 mm @ 700 mm (90%))

Optics


testo 830-T1

**10:1 standard optics,
1 laser beam for spot sighting**




testo 830-T2

Fast measurement value recording at 2 measurements per second, 2 laser beams for sighting




testo 830-T3

**Small measurement point of 2 mm, distance 25 mm,
2 laser beams for sighting**



testo 830-T4

**Distance to measurement spot 30:1,
2 laser beams for sighting**



Accessories

Accessories for all testo 830 versions












Part no.

Adhesive tape, e.g. for bare surfaces (roll, L.: 10 m, W.: 25 mm), E = 0.95, temperature resistant to +250 °C	0554 0051	
Leather case to protect measuring instrument, including belt holder	0516 8302	
9V rech. battery for instrument, instead of battery	0515 0025	
Recharger for 9V rechargeable battery, for external recharging of 0515 0025 battery	0554 0025	
ISO calibration certificate/temperature, infrared thermometer; calibration points +60°C; +120°C; +180°C	0520 0002	

Accessories for testo 830-T2 / -T3 / -T4


ISO calibration certificate/temperature, meas. instr. with surface probe; calibration points +60°C; +120°C; +180°C	0520 0071	
ISO calibration certificate/temperature, for air/immersion probes, calibration point +60°C	0520 0063	
ISO calibration certificate/temperature, for air/immersion probes, calibration points -18°C; 0°C; +60°C	0520 0001	
ISO calibration certificate/temperature, Meas. instr. with air/immersion probe; cal. points 0°C; +150°C; +300°C (Applies only to immersion/penetration probe 0602 2693)	0520 0021	

Probes testo 830-T2 / -T3 / -T4

Probe type	Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	t ₉₉	Part no.
Air probes					
Robust air probe, T/C Type K, Fixed cable 1.2 m		-60 to +400 °C	Class 2*	25 s	0602 1793
Immers./penetr. probes					
Efficient and fast-action immersion probe, waterproof, TC Type K, Fixed cable 1.2 m		-60 to +1000 °C	Class 1*	2 s	0602 0593
Fast-action, waterproof immersion/penetration probe, TC Type K (Calibration not possible over +300 °C), Fixed cable 1.2 m		-60 to +800 °C	Class 1*	3 s	0602 2693
Immersion tip, flexible, TC Type K		-200 to +1000 °C	Class 1*	5 s	0602 5792
Immersion measurement tip, flexible, for measurements in air/exhaust gases (not suitable for measurements in smelters), TC Type K		-200 to +1300 °C	Class 1*	4 s	0602 5693
Immersion tip, flexible, TC Type K		-200 to +40 °C	Class 3*	5 s	0602 5793
Waterproof immersion/penetration probe, TC Type K, Fixed cable 1.2 m		-60 to +400 °C	Class 2*	7 s	0602 1293
Food probes					
Waterproof food probe made of stainless steel (IP65), TC Type K, Fixed cable		-60 to +400 °C	Class 2*	7 s	0602 2292
Robust food probe with special handle, IP 65, reinforced cable (PUR), T/C Type K, Fixed cable		-60 to +400 °C	Class 1*	6 s	0602 2492
Waterproof robust immersion/penetration probe with metal protection hose Tmax +230 °C, e.g. for monitoring temp. in cooking oil, T/C Type K, Fixed cable		-50 to +230 °C	Class 1*	15 s	0628 1292
Thermocouples					
Thermocouple with TC adapter, flexible, 800mm long, fibre glass, TC Type K		-50 to +400 °C	Class 2*	5 s	0602 0644
Thermocouple with TC adapter, flexible, 1500mm long, fibre glass, TC Type K		-50 to +400 °C	Class 2*	5 s	0602 0645
Thermocouple with TC adapter, flexible, 1500mm long, PTFE, TC Type K		-50 to +250 °C	Class 2*	5 s	0602 0646

*According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +1000 °C (Type K), Class 2 to -40 to +1200 °C (Type K), Class 3 to -200 to +40 °C (Type K)

Probes testo 830-T2 / -T3 / -T4

Probe type	Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	t ₉₉	Part no.
Surface probes					
Fast-reaction paddle surface probe, for measurements in inaccessible places, e.g. narrow apertures and slots, TC Type K, Fixed cable		0 to +300 °C	Class 2*	5 s	0602 0193
Fast-action surface probe with sprung thermocouple strip, also for uneven surfaces, measurement range short-term to +500°C, TC Type K, Fixed cable 1.2 m		-60 to +300 °C	Class 2*	3 s	0602 0393
Waterproof surface probe with widened measurement tip for flat surfaces, T/C Type K, Fixed cable 1.2 m		-60 to +400 °C	Class 2*	30 s	0602 1993
Fast-action surface probe with sprung thermocouple strip, bent, also for uneven surfaces, measurement range short-term to +500°C, TC Type K, Fixed cable 1.2 m		-60 to +300 °C	Class 2*	3 s	0602 0993
Efficient, waterproof surface probe with small measurement head for flat surfaces, TC Type K, Fixed cable 1.2 m		-60 to +1000 °C	Class 1*	20 s	0602 0693
Flat head surface probe with telescopic handle max. 680 mm for measurements at hard-to-access points, TC Type K, Fixed cable, 1.6 m (correspondingly shorter when telescope extended)		-50 to +250 °C	Class 2*	3 s	0602 2394
Magnetic probe, adhesive force approx. 20 N, with magnets, for measurements on metal surfaces, TC Type K, Fixed cable		-50 to +170 °C	Class 2*	150 s	0602 4792
Magnetic probe, adhesive force approx. 10 N, with magnets, for higher temp., for measurements on metal surfaces, TC Type K, Fixed cable		-50 to +400 °C	Class 2*		0602 4892
Pipe wrap probe with velcro strip; for temperature measurement on pipes with diameter up to max. 120 mm; Tmax. +120 °C; TC Type K, Fixed cable		-50 to +120 °C	Class 1*	90 s	0628 0020
Pipe wrap probe for pipe diameter 5 to 65 mm, with exchangeable measuring head. Meas. range short-term to +280°C, TC Type K, Fixed cable		-60 to +130 °C	Class 2*	5 s	0602 4592
Spare meas. head for pipe wrap probe, TC Type K		-60 to +130 °C	Class 2*	5 s	0602 0092
Clamp probe for measurements on pipes, pipe diameter 15 to 25 mm (max. 1"), meas. range short-term up to +130°C, TC Type K, Fixed cable		-50 to +100 °C	Class 2*	5 s	0602 4692

*According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +1000 °C (Type K), Class 2 to -40 to +1200 °C (Type K), Class 3 to -200 to +40 °C (Type K)

