

DIN rail bus connectors - HBUS 35,6-16P-1S BK - 2896283

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plug component, Nominal current: 3 A, Pitch: 2.54 mm



Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	12.38 GRM
Custom tariff number	85366990
Country of origin	Germany

Technical data

General

Color	black
-------	-------

Dimensions

Length	37.1 mm
Width	35.6 mm
Pitch	2.54 mm

Technical data

Connection in acc. with standard	CUL
Nominal voltage U_N	60 V
Nominal current I_N	2 A
Indicator1	CUL1
Inflammability class according to UL 94	V0

DIN rail bus connectors - HBUS 35,6-16P-1S BK - 2896283

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

DIN rail bus connectors - HBUS 35,6-16P-1S BK - 2896283

Approvals

UL Recognized	
Nominal current I _N	2 A
Nominal voltage U _N	60 V


cUL Recognized	
Nominal current I _N	2 A
Nominal voltage U _N	60 V

EAC

cULus Recognized	
------------------	--

Drawings

Dimensional drawing



A=35.6 mm

Circuit diagram

