



ELECTORICAL TEST:

- 1: 100% OPEN & SHORT TEST
- 2: CONTACT RESISTANCE : 5 Ω (MAX)
- 3: INSULATION RESISTANCE : 10M Ω /300VDC/10ms(MIN)

Length(mm)	tolerance(mm)	⑧ LABEL "**" character
3050	± 50	03
5000	± 70	05
10000	± 70	10

ITEM	DESCRIPTION	QTY
①	LFH 60pin Male	1
②	V.35 Male	1
③	Outer Molded PVC , CISCO DARK GREEN	2
④	#4-40 screw with DARK GREEN Molded	2
⑤	Screw V.35 Male	1
⑥	Screw V.35 Female	1
⑦	28AWG UL2464 12.5PR Cable OD:8.5mm CISCO DARK GREEN	
⑧	LABEL	1
⑨	Dust Cover	1

packaging



△				Date	2011.11.30	Part No.	CAB-V35MT-**	DWG.No.	CAB-V35MT-**	Version	1.1
△				Design							
△				Check							
Revision	Data	Content	Confirm	Design	Confirm	Customer P/N	ACS-V35MT-**				