

DCX (xxxx) U

SMALL SIGNAL COMPLEMENTARY PRE-BIASED DUAL TRANSISTOR


Features

- Epitaxial Planar Die Construction
- Built-In Biasing Resistors
- Surface Mount Package Suited for Automated Assembly
- **Lead Free/RoHS Compliant (Note 3)**
- **"Green" Device (Note 4 and 5)**


Mechanical Data

- Case: SOT-363
- Case Material: Molded Plastic. "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020D
- Terminals: Solderable per MIL-STD-202, Method 208
- Lead Free Plating (Matte Tin Finish annealed over Alloy 42 leadframe).
- Terminal Connections: See Diagram
- Marking Information: See Page 11
- Ordering Information: See Page 11
- Weight: 0.006 grams (approximate)

P/N	R1	R2	MARKING
DCX124EU	22K Ω	22K Ω	C17
DCX144EU	47K Ω	47K Ω	C20
DCX114YU	10K Ω	47K Ω	C14
DCX123JU	2.2K Ω	47K Ω	C06
DCX114EU	10K Ω	10K Ω	C13
DCX143TU	4.7K Ω	-	C07
DCX143EU	4.7K Ω	4.7K Ω	C08
DCX114TU	10K Ω	-	C12



SOT-363		
Dim	Min	Max
A	0.10	0.30
B	1.15	1.35
C	2.00	2.20
D	0.65 Nominal	
F	0.30	0.40
H	1.80	2.20
J	—	0.10
K	0.90	1.00
L	0.25	0.40
M	0.10	0.25
α	0°	8°
All Dimensions in mm		



Q1: NPN Transistor
Q2: PNP Transistor

SCHEMATIC DIAGRAM

Maximum Ratings NPN Section @T_A = 25°C unless otherwise specified

Characteristic	Symbol	Value	Unit
Supply Voltage, (6) to (1)	V _{CC}	50	V
Input Voltage, (2) to (1)	V _{IN}	-10 to +40 -10 to +40 -6 to +40 -5 to +12 -10 to +40 -5V max -10 to +30 -5V max	V
Output Current	I _O	30 30 70 100 50 100 100 100	mA
Output Current	I _C (Max)	100	mA
Power Dissipation (Total)	P _D	200	mW
Thermal Resistance, Junction to Ambient Air	R _{θJA}	625	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

- Notes:
1. Mounted on FR4 PC Board with recommended pad layout at <http://www.diodes.com/datasheets/ap02001.pdf>.
 2. 150mW per element must not be exceeded.
 3. No purposefully added lead.
 4. Diodes Inc.'s "Green" policy can be found on our website at http://www.diodes.com/products/lead_free/index.php.
 5. Product manufactured with Date Code UO (week 40, 2007) and newer are built with Green Molding Compound. Product manufactured prior to Date Code UO are built with Non-Green Molding Compound and may contain Halogens or Sb₂O₃ Fire Retardants.

Maximum Ratings PNP Section @T_A = 25°C unless otherwise specified

Characteristic		Symbol	Value	Unit
Supply Voltage, (4) to (3)		V _{CC}	50	V
Input Voltage, (5) to (4)	DCX124EU DCX144EU DCX114YU DCX123JU DCX114EU DCX143TU DCX143EU DCX114TU	V _{IN}	+10 to -40 +10 to -40 +6 to -40 +5 to -12 +10 to -40 +5V max +10 to -30 +5V max	V
Output Current	DCX124EU DCX144EU DCX114YU DCX123JU DCX114EU DCX143TU DCX143EU DCX114TU	I _O	-30 -30 -70 -100 -50 -100 -100 -100	mA
Output Current	All	I _C (Max)	-100	mA
Power Dissipation (Total)	(Page 1: Note 2)	P _D	200	mW
Thermal Resistance, Junction to Ambient Air	(Page 1: Note 1)	R _{θJA}	625	°C/W
Operating and Storage Temperature Range		T _J , T _{STG}	-55 to +150	°C


Electrical Characteristics NPN Section @T_A = 25°C unless otherwise specified

Characteristic		Symbol	Min	Typ	Max	Unit	Test Condition
R1 Only (DCX143TU & DCX114TU)							
Collector-Base Breakdown Voltage		BV _{CBO}	50	—	—	V	I _C = 50μA
Collector-Emitter Breakdown Voltage		BV _{CEO}	50	—	—	V	I _C = 1mA
Emitter-Base Breakdown Voltage		BV _{EBO}	5	—	—	V	I _E = 50μA
Collector Cutoff Current		I _{CBO}	—	—	0.5	μA	V _{CB} = 50V
Emitter Cutoff Current		I _{EBO}	—	—	0.5	μA	V _{EB} = 4V
Collector-Emitter Saturation Voltage		V _{CE(sat)}	—	—	0.3	V	I _C /I _B = 2.5mA / 0.25mA DCX143TU I _C /I _B = 1mA / 0.1mA DCX114TU
DC Current Transfer Ratio		h _{FE}	100	250	600	—	I _C = 1mA, V _{CE} = 5V
Input Resistor (R ₁) Tolerance		ΔR ₁	-30	—	+30	%	—
Gain-Bandwidth Product		f _T	—	250	—	MHz	V _{CE} = 10V, I _E = -5mA, f = 100MHz
R1/R2 Only							
Input Voltage	DCX124EU	V _{I(off)}	0.5	1.1	—	V	V _{CC} = 5V, I _O = 100μA
	DCX144EU		0.5	1.1			
	DCX114YU		0.3	—			
	DCX123JU		0.5	—			
	DCX114EU		0.5	1.1			
	DCX143EU		0.5	1.16			
	DCX124EU	V _{I(on)}	—	1.9	3.0		V _O = 0.3, I _O = 5mA
	DCX144EU		—	1.9	3.0		V _O = 0.3, I _O = 2mA
	DCX114YU		—	—	1.4		V _O = 0.3, I _O = 1mA
	DCX123JU		—	—	1.1		V _O = 0.3, I _O = 5mA
	DCX114EU		—	1.9	3.0		V _O = 0.3, I _O = 10mA
	DCX143EU		—	1.99	3.0		V _O = 0.3, I _O = 20mA
Output Voltage	DCX124EU	V _{O(on)}	—	0.1	0.3	V	I _O /I _I = 10mA / 0.5mA
	DCX144EU						I _O /I _I = 10mA / 0.5mA
	DCX114YU						I _O /I _I = 5mA / 0.25mA
	DCX123JU						I _O /I _I = 5mA / 0.25mA
	DCX114EU						I _O /I _I = 10mA / 0.5mA
	DCX143EU						I _O /I _I = 10mA / 0.5mA
Input Current	DCX124EU	I _I	—	—	0.36	mA	V _I = 5V
	DCX144EU				0.18		
	DCX114YU				0.88		
	DCX123JU				3.6		
	DCX114EU				0.88		
	DCX143EU				0.88		
Output Current		I _{O(off)}	—	—	0.5	μA	V _{CC} = 50V, V _I = 0V
DC Current Gain	DCX124EU	G _I	56	—	—	—	V _O = 5V, I _O = 5mA
	DCX144EU		68				V _O = 5V, I _O = 5mA
	DCX114YU		68				V _O = 5V, I _O = 10mA
	DCX123JU		80				V _O = 5V, I _O = 10mA
	DCX114EU		30				V _O = 5V, I _O = 5mA
	DCX143EU		50				V _O = 5V, I _O = 10mA
Input Resistor (R ₁) Tolerance		ΔR ₁	-30	—	+30	%	—
Resistance Ratio Tolerance		R ₂ /R ₁	-20	—	+20	%	—
Gain-Bandwidth Product		f _T	—	250	—	MHz	V _{CE} = 10V, I _E = 5mA, f = 100MHz





Electrical Characteristics PNP Section @T_A = 25°C unless otherwise specified

Characteristic		Symbol	Min	Typ	Max	Unit	Test Condition
R1 Only (DCX143TU & DCX114TU)							
Collector-Base Breakdown Voltage		BV _{CBO}	-50	—	—	V	I _C = -50μA
Collector-Emitter Breakdown Voltage		BV _{CEO}	-50	—	—	V	I _C = -1mA
Emitter-Base Breakdown Voltage		BV _{EBO}	-5	—	—	V	I _E = -50μA
Collector Cutoff Current		I _{CBO}	—	—	-0.5	μA	V _{CB} = -50V
Emitter Cutoff Current		I _{EBO}	—	—	-0.5	μA	V _{EB} = -4V
Collector-Emitter Saturation Voltage		V _{CE(sat)}	—	—	-0.3	V	I _C /I _B = 2.5mA / 0.25mA DCX143TU I _C /I _B = 1mA / 0.1mA DCX114TU
DC Current Transfer Ratio		h _{FE}	100	250	600	—	I _C = -1mA, V _{CE} = -5V
Input Resistor (R ₁) Tolerance		ΔR ₁	-30	—	+30	%	—
Gain-Bandwidth Product		f _T	—	250	—	MHz	V _{CE} = -10V, I _E = 5mA, f = 100MHz
R1/R2 Only							
Input Voltage	DCX124EU	V _{I(off)}	-0.5	-1.1	—	V	V _{CC} = -5V, I _O = -100μA
	DCX144EU		-0.5	-1.1	—		
	DCX114YU		-0.3	—	—		
	DCX123JU		-0.5	—	—		
	DCX114EU		-0.5	-1.1	—		
	DCX143EU		-0.5	-1.16	—		
	DCX124EU	V _{I(on)}	—	-1.9	-3.0		V _O = -0.3, I _O = -5mA
	DCX144EU		—	-1.9	-3.0		V _O = -0.3, I _O = -2mA
	DCX114YU		—	—	-1.4		V _O = -0.3, I _O = -1mA
	DCX123JU		—	—	-1.1		V _O = -0.3, I _O = -5mA
	DCX114EU		—	-1.9	-3.0		V _O = -0.3, I _O = -10mA
	DCX143EU		—	-2.5	-3.0		V _O = -0.3, I _O = -20mA
Output Voltage	DCX124EU	V _{O(on)}	—	-0.1	-0.3	V	I _O /I _I = -10mA / -0.5mA
	DCX144EU		—				I _O /I _I = -10mA / -0.5mA
	DCX114YU		—				I _O /I _I = -5mA / -0.25mA
	DCX123JU		—				I _O /I _I = -5mA / -0.25mA
	DCX114EU		—				I _O /I _I = -10mA / -0.5mA
	DCX143EU		—				I _O /I _I = -10mA / -0.5mA
Input Current	DCX124EU	I _I	—	—	-0.36	mA	V _I = -5V
	DCX144EU		—		-0.18		
	DCX114YU		—		-0.88		
	DCX123JU		—		-3.6		
	DCX114EU		—		-0.88		
	DCX143EU		—		-0.88		
Output Current		I _{O(off)}	—	—	-0.5	μA	V _{CC} = 50V, V _I = 0V
DC Current Gain	DCX124EU	G _I	56	—	—	—	V _O = -5V, I _O = -5mA
	DCX144EU		68				V _O = -5V, I _O = -5mA
	DCX114YU		68				V _O = -5V, I _O = -10mA
	DCX123JU		80				V _O = -5V, I _O = -10mA
	DCX114EU		30				V _O = -5V, I _O = -5mA
	DCX143EU		40				V _O = -5V, I _O = -10mA
Input Resistor (R ₁) Tolerance		ΔR ₁	-30	—	+30	%	—
Resistance Ratio Tolerance		R ₂ /R ₁	-20	—	+20	%	—
Gain-Bandwidth Product		f _T	—	250	—	MHz	V _{CE} = -10V, I _E = -5mA, f = 100MHz

Typical Curves – Total Device



Typical Curves – DCX123JU PNP Section



Typical Curves – DCX123JU PNP Section (Continued)




Fig. 6 Typical Input Voltage vs. Collector Current

Typical Curves – DCX123JU NPN Section




Fig. 7 Typical $V_{CE(SAT)}$ vs. I_C




Fig. 8 Typical DC Current Gain




Fig. 9 Typical Output Capacitance









Fig. 10 Typical Collector Current vs. Input Voltage

Typical Curves – DCX123JU NPN Section (Continued)



Typical Curves – DCX143EU PNP Section



Typical Curves – DCX143EU PNP Section (Continued)




Fig. 16 Typical $V_{BE(SAT)}$ vs. I_C




Fig. 17 Typical $V_{I(ON)}$ vs. I_C

Typical Curves – DCX143EU NPN Section




Fig. 18 Typical V_{CE} vs. I_C




Fig. 19 Typical DC Current Gain




Fig. 20 Typical $V_{CE(SAT)}$ vs. I_C










Fig. 21 Typical V_{BE} vs. I_C

Typical Curves – DCX143EU NPN Section (Continued)



Typical Curves – DCX114TU PNP Section



Typical Curves – DCX114TU PNP Section (Continued)




Fig. 28 Typical Input Voltage vs. Collector Current

Typical Curves – DCX114TU NPN Section




Fig. 29 Typical $V_{CE(SAT)}$ vs. I_C




Fig. 30 Typical DC Current Gain




Fig. 31 Typical Output Capacitance




Fig. 32 Typical Collector Current vs. Input Voltage

Typical Curves – DCX114TU NPN Section (Continued)





Fig. 33 Typical Input Voltage vs. Collector Current

Ordering Information (Note 6)

Device	Packaging	Shipping
DCX124EU-7-F	SOT-363	3000/Tape & Reel
DCX144EU-7-F	SOT-363	3000/Tape & Reel
DCX114YU-7-F	SOT-363	3000/Tape & Reel
DCX123JU-7-F	SOT-363	3000/Tape & Reel
DCX114EU-7-F	SOT-363	3000/Tape & Reel
DCX143TU-7-F	SOT-363	3000/Tape & Reel
DCX143EU-7-F	SOT-363	3000/Tape & Reel
DCX114TU-7-F	SOT-363	3000/Tape & Reel

Notes: 6. For packaging details, go to our website at <http://www.diodes.com/datasheets/ap02007.pdf>.

Marking Information




CXX = Product Type Marking Code
 YM = Date Code Marking
 Y = Year ex: T = 2006
 M = Month ex: 9 = September

Date Code Key

Year	2006	2007	2008	2009	2010	2011	2012	2013	2014	2015
Code	T	U	V	W	X	Y	Z	A	B	C

Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	O	N	D

Suggested Pad Layout



Dimensions	Value (in mm)
Z	2.5
G	1.3
X	0.42
Y	0.6
C	1.9
E	0.65

IMPORTANT NOTICE

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Diodes Incorporated does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

Diodes Incorporated products are not authorized for use as critical components in life support devices or systems without the expressed written approval of the President of Diodes Incorporated.