

## Single phase, non-stabilised dc power supply **GLC 230/24-5**



### Advantages

- Fuse protection in the input and a fuse protection for the output
- Separate windings
- Capacitor accessories
- Double screw terminals on the output
- DC OK signalling via LEDs
- Panel installation on mounting rails

### Applications

Robust direct current power is concentrated on the core task of voltage and power supply.

### Standards



Control transformer  
to: VDE 0570 Teil 2-2, DIN EN 61558-2-2, EN 61558-2-2, IEC 61558-2-2,  
UL 5085-1/-2, CSA 22.2 No.66

### Approvals




UL 5085-1/-2, CSA 22.2 No.66



# Single phase, non-stabilised dc power supply GLC 230/24-5

Type		GLC 230/24-5
Electrical data	<b>Input</b>	
	Input rated voltage	230 Vac
	Rated frequency	50 - 60 Hz
	<b>Output</b>	
	Output rated voltage	24 Vdc
	Power	120.00 W
	Output rated current	5.00 A
	Ripple factor	#5 %
	<b>Standards</b>	
	Classification	Single phase non-stabilised dc power supply / safety isolating transformer
	<b>Approvals</b>	
	Approvals	cURus (transformer only)
	<b>Environment</b>	
	Cooling method	by self cooling
	Ambient temperature max.	60° C
<b>Safety and protection</b>		
Type	enclosed	
Class of Insulation System	E	
Protection index	IP 00	
Safety class (prepared)	II	
Short circuit strength	short-circuit proof	
<b>Order numbers</b>		
<b>Order Number</b>	<b>GLC 230/24-5</b>	

Type		GLC 230/24-5
Mechanical data	<b>Terminal and mounting</b>	
	Terminals	Screw-type terminals
	Fixing method	DIN Rail system TH 35, additional with screws
	<b>Measures and weights</b>	
	Weight	3.50 kg



Subjects to change.