

# Snap-in markers - UC-EMP (17X15) - 0825421

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Snap-in markers, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: snapped into marker carrier, Lettering field: 17 x 15 mm



## Why buy this product

- The UC-EMP ... UniCard labeling range includes markers that can be fitted into existing CARRIER-EMP ... label frames
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The format automatically ensures printing with a high degree of positioning accuracy
- The sheets provide space for including function texts



## Key commercial data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 10 pc                                                                                                   |
| Minimum order quantity               | 10 pc                                                                                                   |
| GTIN                                 | <br>4 046356 365789 |
| Weight per Piece (excluding packing) | 6.2 g                                                                                                   |
| Custom tariff number                 | 39269097                                                                                                |
| Country of origin                    | Poland                                                                                                  |

## Technical data

### Dimensions

|            |       |
|------------|-------|
| Length (b) | 17 mm |
| Width (a)  | 15 mm |

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

### General

|                                         |                                |
|-----------------------------------------|--------------------------------|
| Color                                   | white                          |
| Components                              | free from silicone and halogen |
| Inflammability class according to UL 94 | V2                             |

# Snap-in markers - UC-EMP (17X15) - 0825421

## Technical data

### General

|                                                                     |                                     |
|---------------------------------------------------------------------|-------------------------------------|
| Material                                                            | PA                                  |
| Wipe resistance                                                     | DIN EN 61010-1 (VDE 0411-1)         |
| Number of individual labels                                         | 8                                   |
| Number of individual labels per row                                 | 2                                   |
| Printability                                                        | Inkjet printing                     |
|                                                                     | Plotter                             |
| Device                                                              | 5147888 BLUEMARK LED                |
|                                                                     | 5147999 BLUEMARK CLED               |
|                                                                     | 5144615 CMS-P1-PLOTTER              |
|                                                                     | 5146121 P1 UC-MAG 6                 |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result                                                              | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration                                                       | 96 h                                |
| Wipe resistance test result                                         | Test passed                         |
| Salt spray test specification                                       | DIN EN ISO 9227:2012-09             |
| Test duration                                                       | 96 h                                |
| Salt spray testing result                                           | Test passed                         |
| Alternating condensation climate with SO2 test specification        | Following DIN 50018:2013-05         |
| Climate level                                                       | AHT 1.0 S                           |
| Cycles                                                              | 2                                   |
| Condensation test result                                            | Test passed                         |
| Wipe resistance of test specification inscriptions                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result                                                              | Test passed                         |
| Marking mounting type                                               | snapped into marker carrier         |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |

# Snap-in markers - UC-EMP (17X15) - 0825421

## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 5.0 | EC000761 |
|----------|----------|

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |

## Accessories

### Accessories

#### Magazine

Magazine - P1 UC-MAG 6 - 5146121



Magazine, for CMS-P1-PLOTTER, for accommodating UC-EMP..., UC-EMLP...

---

### Marker carriers

Marker carriers - CARRIER-EMP (17X15) - 0827450



Marker carriers, black, unlabeled, Mounting type: Screws, rivets, Lettering field: 17 x 15 mm

---

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366



Profile, for screwing or riveting, 1000 mm long, for accommodating UC und US materials, height: 15 mm

---

## Snap-in markers - UC-EMP (17X15) - 0825421

### Accessories

Marker carriers - CARRIER-EMP (1000X15) TR - 0829530



Marker carriers, transparent, unlabeled, Mounting type: Screws, rivets, Lettering field: 1000 x 15 mm

---

Marker carriers - CARRIER/L-EMP (1000X15) GY - 0829559



Profile, self-adhesive, 1000 mm long, for accommodating UC and US materials, height: 15 mm

---

Marker carriers - CARRIER/L-EMP (1000X15) TR - 0829560



Marker carriers, transparent, unlabeled, Mounting type: Adhesive, Lettering field: 1000 x 15 mm

---

---