

Datasheet

RS Pro PUR 5m Long transparent Flexible Ducting Reinforced, 63mm Bend Radius, Applications Various

RS Stock No: **399-0805**



Product Details

RS Pro 5 m long reinforced transparent flexible ducting features polyurethane (PU) hosing with a copper plated steel spiral for durability. The ducting has 63 mm bend radius and is suitable for suction and the transport of dusts, chips and abrasive materials. The hose offers excellent internal and external abrasion resistance. It is also suitable for oil and petrol fume extraction.

Features and Benefits

- Copper coated spring steel spiral helix between 2 layers of crystal clear flexible polyurethane
- Excellent internal and external abrasion resistance
- Retains full diameter even in tight bending radii
- Suitable for the transfer of large abrasive particles such as sawdust, timber off cuts and metal swarf
- Also suitable for oil and petrol fume extraction
- Temperature range from -40 to +90°C

**Specifications:**

Bend Radius	63 mm
Colour	Transparent
Inner Diameter	63 mm
Length	5 m
Material	PUR
Outer Diameter	68
Reinforced	Yes
Suitable Applications	Abrasive Material, Chemical, Dust, Granule, Saw Dust, Oil & Petrol Fume Extraction
Wall Thickness	0.7 mm
Operating Temperature	-25 to +125°C